

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684185

Luminaire Tested: **LX6C30D010 EX6C309035 6LBMDH**

Issue Date: 2/15/2022



**Test Information**


Test Method: LM-79-08  
Report Number: P684185  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C30D010 EX6C309035 6LBMDH  
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2202.0 lumens  
Efficiency: N/A  
Efficacy: 69.7 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684185  
CATALOG NUMBER: LX6C30D010 EX6C309035 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P684185

CATALOG NUMBER: LX6C30D010 EX6C309035 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	158661
5°	153753
10°	141581
15°	126987
20°	112990
25°	93828
30°	67036
35°	43092
40°	26256
45°	14598
50°	6465
55°	3747
60°	2467
65°	1751
70°	1234
75°	953
80°	600
85°	377



TEST NUMBER: P684185

CATALOG NUMBER: LX6C30D010 EX6C309035 6LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	258.6	11.7
10°-20°	626.0	28.4
20°-30°	696.2	31.6
30°-40°	412.5	18.7
40°-50°	151.1	6.9
50°-60°	38.0	1.7
60°-70°	13.9	0.6
70°-80°	4.8	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1580.8	71.8
0°-40°	1993.3	90.5
0°-60°	2182.4	99.1
0°-90°	2202.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2202.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2894	
5°	2794	259
15°	2238	626
25°	1551	696
35°	644	413
45°	188	151
55°	39	38
65°	14	14
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P684185

CATALOG NUMBER: LX6C30D010 EX6C309035 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2894.2
2.5°	2868.5
5°	2794.0
7.5°	2680.9
10°	2543.4
12.5°	2391.7
15°	2237.5
17.5°	2087.8
20°	1936.8
22.5°	1761.3
25°	1551.2
27.5°	1309.6
30°	1059.0
32.5°	834.7
35°	643.9
37.5°	489.0
40°	366.9
42.5°	267.3
45°	188.3
47.5°	119.5
50°	75.8
52.5°	53.3
55°	39.2
57.5°	29.6
60°	22.5
62.5°	17.3
65°	13.5
67.5°	10.3
70°	7.7
72.5°	5.8
75°	4.5
77.5°	3.2
80°	1.9
82.5°	1.3
85°	0.6
87.5°	0.6
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)