

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856626

Luminaire Tested: **LD6C30D010 EU6309040 6LBWLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856626  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C30D010 EU6309040 6LBWLI  
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3081.9 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856626

CATALOG NUMBER: LD6C30D010 EU6309040 6LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856626

CATALOG NUMBER: LD6C30D010 EU6309040 6LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92	92	92	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83	83	83	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76	76	76	76
4	93	85	78	74	92	84	78	73	81	76	72	79	75	71	77	74	70	69	69	69	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63	63	63	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57	57	57	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52	52	52	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48	48	48	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44	44	44	44
10	65	54	47	43	64	53	47	43	52	46	42	51	46	42	51	46	42	41	41	41	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	105551
5°	106526
10°	109506
15°	112248
20°	113952
25°	111599
30°	104630
35°	93545
40°	75771
45°	50121
50°	25330
55°	10685
60°	3443
65°	1349
70°	1122
75°	741
80°	0
85°	0



TEST NUMBER: P856626

CATALOG NUMBER: LD6C30D010 EU6309040 6LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	185.7	6.0
10°-20°	558.3	18.1
20°-30°	841.6	27.3
30°-40°	861.4	27.9
40°-50°	501.8	16.3
50°-60°	115.3	3.7
60°-70°	14.1	0.5
70°-80°	3.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1585.6	51.4
0°-40°	2447.0	79.4
0°-60°	3064.1	99.4
0°-90°	3081.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3081.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1925	
5°	1936	186
15°	1978	558
25°	1845	842
35°	1398	861
45°	646	502
55°	112	115
65°	10	14
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P856626

CATALOG NUMBER: LD6C30D010 EU6309040 6LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1925.4
2.5°	1921.9
5°	1935.8
7.5°	1949.8
10°	1967.2
12.5°	1970.8
15°	1977.8
17.5°	1970.8
20°	1953.3
22.5°	1897.4
25°	1845.0
27.5°	1761.2
30°	1652.9
32.5°	1541.0
35°	1397.8
37.5°	1236.9
40°	1058.8
42.5°	859.6
45°	646.5
47.5°	450.7
50°	297.0
52.5°	188.7
55°	111.8
57.5°	59.4
60°	31.4
62.5°	17.5
65°	10.4
67.5°	10.4
70°	7.0
72.5°	3.5
75°	3.5
77.5°	3.5
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)