

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684537

Luminaire Tested: **LX6C70D010 EX6C709035 6LBMH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C70D010 EX6C709035 6LBMH
Description: 6 INCH 7000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5309.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 78
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684537

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P684537

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	288031
5°	282874
10°	268421
15°	251710
20°	234415
25°	215988
30°	179971
35°	126846
40°	80837
45°	48207
50°	28460
55°	18102
60°	12466
65°	8847
70°	6091
75°	4808
80°	2368
85°	0



TEST NUMBER: P684537

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	480.4	9.0
10°-20°	1242.8	23.4
20°-30°	1610.3	30.3
30°-40°	1195.5	22.5
40°-50°	504.7	9.5
50°-60°	179.2	3.4
60°-70°	69.2	1.3
70°-80°	23.9	0.5
80°-90°	3.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3333.5	62.8
0°-40°	4529.0	85.3
0°-60°	5212.8	98.2
0°-90°	5309.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5309.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5254	
5°	5140	480
15°	4435	1243
25°	3571	1610
35°	1895	1196
45°	622	505
55°	189	179
65°	68	69
75°	23	24
85°	0	3
90°	0	



TEST NUMBER: P684537

CATALOG NUMBER: LX6C70D010 EX6C709035 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	5254.1
2.5°	5238.8
5°	5140.4
7.5°	4996.1
10°	4822.0
12.5°	4632.3
15°	4435.1
17.5°	4215.4
20°	4018.2
22.5°	3813.5
25°	3570.8
27.5°	3237.2
30°	2843.1
32.5°	2380.5
35°	1895.4
37.5°	1486.0
40°	1129.6
42.5°	841.5
45°	621.8
47.5°	454.8
50°	333.7
52.5°	250.2
55°	189.4
57.5°	143.9
60°	113.7
62.5°	83.5
65°	68.2
67.5°	53.0
70°	38.0
72.5°	30.2
75°	22.7
77.5°	15.3
80°	7.5
82.5°	7.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)