

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684954

Luminaire Tested: **LX6C30D010 EX6309040 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684954
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C30D010 EX6309040 6LBSLI
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3288.0 lumens
Efficiency: N/A
Efficacy: 104.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684954
CATALOG NUMBER: LX6C30D010 EX6309040 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P684954

CATALOG NUMBER: LX6C30D010 EX6309040 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	113746
5°	112447
10°	106750
15°	98525
20°	90074
25°	81561
30°	74296
35°	68730
40°	64242
45°	59843
50°	54514
55°	47740
60°	39832
65°	31261
70°	21831
75°	11840
80°	2210
85°	0



TEST NUMBER: P684954

CATALOG NUMBER: LX6C30D010 EX6309040 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	191.2	5.8
10°-20°	486.7	14.8
20°-30°	620.7	18.9
30°-40°	643.7	19.6
40°-50°	593.1	18.0
50°-60°	446.2	13.6
60°-70°	240.8	7.3
70°-80°	64.6	2.0
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.7	39.5
0°-40°	1942.4	59.1
0°-60°	2981.6	90.7
0°-90°	3288.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3288.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2075	
5°	2043	191
15°	1736	487
25°	1348	621
35°	1027	644
45°	772	593
55°	500	446
65°	241	241
75°	56	65
85°	0	1
90°	0	



TEST NUMBER: P684954

CATALOG NUMBER: LX6C30D010 EX6309040 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2074.9
2.5°	2067.9
5°	2043.4
7.5°	1998.0
10°	1917.7
12.5°	1837.4
15°	1736.0
17.5°	1641.8
20°	1544.0
22.5°	1442.7
25°	1348.4
27.5°	1257.5
30°	1173.7
32.5°	1096.8
35°	1027.0
37.5°	960.6
40°	897.7
42.5°	831.4
45°	771.9
47.5°	705.6
50°	639.2
52.5°	569.4
55°	499.5
57.5°	429.7
60°	363.3
62.5°	300.4
65°	241.0
67.5°	185.1
70°	136.2
72.5°	94.3
75°	55.9
77.5°	24.4
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)