

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684195

Luminaire Tested: **LX6C30D010 EX6C309040 6LBSH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684195  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C30D010 EX6C309040 6LBSH  
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3176.0 lumens  
Efficiency: N/A  
Efficacy: 100.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684195

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684195

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	91062
5°	90634
10°	88765
15°	85534
20°	81604
25°	77206
30°	72828
35°	68569
40°	64564
45°	60185
50°	54881
55°	48467
60°	41027
65°	32208
70°	22985
75°	12581
80°	2210
85°	0



TEST NUMBER: P684195

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	155.6	4.9
10°-20°	422.9	13.3
20°-30°	587.3	18.5
30°-40°	640.9	20.2
40°-50°	597.8	18.8
50°-60°	453.8	14.3
60°-70°	248.5	7.8
70°-80°	68.4	2.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1165.7	36.7
0°-40°	1806.6	56.9
0°-60°	2858.2	90.0
0°-90°	3176.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3176.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1661	
5°	1647	156
15°	1507	423
25°	1276	587
35°	1025	641
45°	776	598
55°	507	454
65°	248	248
75°	59	68
85°	0	1
90°	0	



TEST NUMBER: P684195

CATALOG NUMBER: LX6C30D010 EX6C309040 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1661.1
2.5°	1661.1
5°	1647.0
7.5°	1626.0
10°	1594.6
12.5°	1552.6
15°	1507.1
17.5°	1451.2
20°	1398.8
22.5°	1335.8
25°	1276.4
27.5°	1216.9
30°	1150.5
32.5°	1087.5
35°	1024.6
37.5°	961.7
40°	902.2
42.5°	839.3
45°	776.3
47.5°	713.4
50°	643.5
52.5°	577.0
55°	507.1
57.5°	440.6
60°	374.2
62.5°	307.8
65°	248.3
67.5°	192.3
70°	143.4
72.5°	97.9
75°	59.4
77.5°	28.0
80°	7.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)