

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P583009

Luminaire Tested: **LX6C75D010 EU6759030 6LBHYLI**

Issue Date: 8/31/2023



Test Information

Test Method: LM-79-08
Report Number: P583009
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2301-896-1)
Test Lab: INNOVATION CENTER
Issue Date: 8/31/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EU6759030 6LBHYLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LCHYP TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5552.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.52
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P583009

CATALOG NUMBER: LX6C75D010 EU6759030 6LBHYLI

Luminous Intensity Polar Plot





TEST NUMBER: P583009

CATALOG NUMBER: LX6C75D010 EU6759030 6LBHYLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92			
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89			
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85			
5	100	94	89	86	98	93	89	86	91	87	85	89	86	84	88	85	83	82			
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79			
7	93	87	82	79	92	86	82	79	85	81	78	84	80	78	83	80	78	76			
8	91	83	79	76	90	83	79	76	82	78	75	81	78	75	80	77	75	74			
9	88	81	76	73	87	80	76	73	79	76	73	79	75	73	78	75	72	71			
10	85	78	74	71	84	78	73	71	77	73	70	76	73	70	76	72	70	69			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	941536
5°	917761
10°	778092
15°	504328
20°	313196
25°	168572
30°	57939
35°	23336
40°	6240
45°	2783
50°	1092
55°	487
60°	285
65°	337
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P583009

CATALOG NUMBER: LX6C75D010 EU6759030 6LBHYLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1504.3	27.1
10°-20°	2481.0	44.7
20°-30°	1286.3	23.2
30°-40°	243.6	4.4
40°-50°	30.7	0.6
50°-60°	4.5	0.1
60°-70°	1.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5271.6	94.9
0°-40°	5515.2	99.3
0°-60°	5550.5	100.0
0°-90°	5552.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5552.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	17175	
5°	16678	###
15°	8886	2481
25°	2787	1286
35°	349	244
45°	36	31
55°	5	5
65°	3	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P583009

CATALOG NUMBER: LX6C75D010 EU6759030 6LBHYLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	17175.0
2.5°	17146.7
5°	16677.6
7.5°	15600.8
10°	13977.9
12.5°	11534.6
15°	8886.2
17.5°	6747.9
20°	5368.6
22.5°	4002.1
25°	2786.9
27.5°	1712.6
30°	915.3
32.5°	617.9
35°	348.7
37.5°	151.3
40°	87.2
42.5°	56.4
45°	35.9
47.5°	20.5
50°	12.8
52.5°	5.1
55°	5.1
57.5°	2.6
60°	2.6
62.5°	2.6
65°	2.6
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)