

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685194

Luminaire Tested: **LX6C75D010 EX6759030 6LBSLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P685194  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C75D010 EX6759030 6LBSLI  
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9078.0 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685194

CATALOG NUMBER: LX6C75D010 EX6759030 6LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685194

CATALOG NUMBER: LX6C75D010 EX6759030 6LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	314043
5°	310466
10°	294728
15°	272028
20°	248685
25°	225176
30°	205120
35°	189760
40°	177368
45°	165234
50°	150520
55°	131809
60°	109969
65°	86313
70°	60283
75°	32661
80°	6125
85°	0



TEST NUMBER: P685194

CATALOG NUMBER: LX6C75D010 EX6759030 6LBSLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	527.9	5.8
10°-20°	1343.9	14.8
20°-30°	1713.7	18.9
30°-40°	1777.2	19.6
40°-50°	1637.6	18.0
50°-60°	1231.8	13.6
60°-70°	664.9	7.3
70°-80°	178.3	2.0
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3585.5	39.5
0°-40°	5362.7	59.1
0°-60°	8232.1	90.7
0°-90°	9078.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9078.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5729	
5°	5642	528
15°	4793	1344
25°	3723	1714
35°	2836	1777
45°	2131	1638
55°	1379	1232
65°	665	665
75°	154	178
85°	0	3
90°	0	



TEST NUMBER: P685194

CATALOG NUMBER: LX6C75D010 EX6759030 6LBSLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5728.6
2.5°	5709.5
5°	5641.8
7.5°	5516.5
10°	5294.6
12.5°	5072.9
15°	4793.1
17.5°	4532.9
20°	4262.8
22.5°	3983.2
25°	3722.7
27.5°	3472.0
30°	3240.4
32.5°	3028.3
35°	2835.5
37.5°	2652.1
40°	2478.5
42.5°	2295.4
45°	2131.3
47.5°	1948.2
50°	1764.9
52.5°	1572.1
55°	1379.1
57.5°	1186.3
60°	1003.0
62.5°	829.3
65°	665.4
67.5°	511.2
70°	376.1
72.5°	260.4
75°	154.2
77.5°	67.4
80°	19.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)