

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684570

Luminaire Tested: **LX6C75D010 EX6C759030 6LBNH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684570
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6C759030 6LBNH
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5295.0 lumens
Efficiency: N/A
Efficacy: 65.0 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684570

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684570

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93																											
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																											
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																											
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75																											
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70																											
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65																											
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61																											
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58																											
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54																											
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	372103
5°	362893
10°	334847
15°	296455
20°	257407
25°	220168
30°	181515
35°	119531
40°	64256
45°	28445
50°	11539
55°	8325
60°	5285
65°	3775
70°	3109
75°	2055
80°	3062
85°	0



TEST NUMBER: P684570

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	610.4	11.5
10°-20°	1455.6	27.5
20°-30°	1667.6	31.5
30°-40°	1120.4	21.2
40°-50°	320.1	6.0
50°-60°	78.4	1.5
60°-70°	29.8	0.6
70°-80°	11.5	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3733.5	70.5
0°-40°	4853.9	91.7
0°-60°	5252.4	99.2
0°-90°	5295.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5295.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6788	
5°	6594	610
15°	5224	1456
25°	3640	1668
35°	1786	1120
45°	367	320
55°	87	78
65°	29	30
75°	10	12
85°	0	1
90°	0	



TEST NUMBER: P684570

CATALOG NUMBER: LX6C75D010 EX6C759030 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6787.7
2.5°	6739.4
5°	6594.5
7.5°	6333.7
10°	6015.3
12.5°	5609.5
15°	5223.5
17.5°	4818.1
20°	4412.3
22.5°	4026.3
25°	3639.9
27.5°	3282.7
30°	2867.5
32.5°	2317.1
35°	1786.1
37.5°	1303.4
40°	897.9
42.5°	588.9
45°	366.9
47.5°	222.0
50°	135.3
52.5°	106.1
55°	87.1
57.5°	67.6
60°	48.2
62.5°	38.5
65°	29.1
67.5°	19.4
70°	19.4
72.5°	9.7
75°	9.7
77.5°	9.7
80°	9.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)