

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563928

Luminaire Tested: **LX6C30D010 EX6C309030 6LBMH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563928
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C30D010 EX6C309030 6LBMH
Description: 6 INCH 3000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2232.7 lumens
Efficiency: N/A
Efficacy: 70.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 31.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563928

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P563928

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	121136
5°	118968
10°	112885
15°	105858
20°	98586
25°	90840
30°	75689
35°	53344
40°	33992
45°	20273
50°	11965
55°	7608
60°	5241
65°	3723
70°	2565
75°	2033
80°	1010
85°	0



TEST NUMBER: P563928

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	202.0	9.0
10°-20°	522.7	23.4
20°-30°	677.2	30.3
30°-40°	502.8	22.5
40°-50°	212.2	9.5
50°-60°	75.3	3.4
60°-70°	29.1	1.3
70°-80°	10.1	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1401.9	62.8
0°-40°	1904.7	85.3
0°-60°	2192.3	98.2
0°-90°	2232.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2232.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2210	
5°	2162	202
15°	1865	523
25°	1502	677
35°	797	503
45°	262	212
55°	80	75
65°	29	29
75°	10	10
85°	0	1
90°	0	



TEST NUMBER: P563928

CATALOG NUMBER: LX6C30D010 EX6C309030 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2209.7
2.5°	2203.3
5°	2161.9
7.5°	2101.1
10°	2027.9
12.5°	1948.1
15°	1865.2
17.5°	1772.9
20°	1689.9
22.5°	1603.8
25°	1501.8
27.5°	1361.4
30°	1195.7
32.5°	1001.1
35°	797.1
37.5°	625.0
40°	475.0
42.5°	353.9
45°	261.5
47.5°	191.3
50°	140.3
52.5°	105.2
55°	79.6
57.5°	60.5
60°	47.8
62.5°	35.1
65°	28.7
67.5°	22.3
70°	16.0
72.5°	12.7
75°	9.6
77.5°	6.4
80°	3.2
82.5°	3.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)