

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685199

Luminaire Tested: **LX6C75D010 EX6759035 6LBSLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685199
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6759035 6LBSLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9205.0 lumens
Efficiency: N/A
Efficacy: 112.9 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685199
CATALOG NUMBER: LX6C75D010 EX6759035 6LBSLI

Luminous Intensity Polar Plot





TEST NUMBER: P685199

CATALOG NUMBER: LX6C75D010 EX6759035 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89																			
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77																			
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68																			
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60																			
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53																			
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47																			
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43																			
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39																			
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36																			
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	318439
5°	314813
10°	298853
15°	275836
20°	252162
25°	228328
30°	207994
35°	192411
40°	179851
45°	167545
50°	152626
55°	133654
60°	111504
65°	87519
70°	61132
75°	33127
80°	6219
85°	0



TEST NUMBER: P685199

CATALOG NUMBER: LX6C75D010 EX6759035 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	535.3	5.8
10°-20°	1362.7	14.8
20°-30°	1737.7	18.9
30°-40°	1802.1	19.6
40°-50°	1660.5	18.0
50°-60°	1249.1	13.6
60°-70°	674.2	7.3
70°-80°	180.9	2.0
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3635.7	39.5
0°-40°	5437.7	59.1
0°-60°	8347.3	90.7
0°-90°	9205.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9205.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5809	
5°	5721	535
15°	4860	1363
25°	3775	1738
35°	2875	1802
45°	2161	1660
55°	1398	1249
65°	675	674
75°	156	181
85°	0	3
90°	0	



TEST NUMBER: P685199

CATALOG NUMBER: LX6C75D010 EX6759035 6LBSLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	5808.8
2.5°	5789.3
5°	5720.8
7.5°	5593.6
10°	5368.7
12.5°	5143.9
15°	4860.2
17.5°	4596.3
20°	4322.4
22.5°	4038.9
25°	3774.8
27.5°	3520.6
30°	3285.8
32.5°	3070.6
35°	2875.1
37.5°	2689.2
40°	2513.2
42.5°	2327.5
45°	2161.1
47.5°	1975.4
50°	1789.6
52.5°	1594.1
55°	1398.4
57.5°	1202.9
60°	1017.0
62.5°	840.9
65°	674.7
67.5°	518.3
70°	381.4
72.5°	264.1
75°	156.4
77.5°	68.4
80°	19.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)