

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684577

Luminaire Tested: **LX6C75D010 EX6C759035 6LBNH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6C759035 6LBNH
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBN TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5369.9 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684577

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBNH

Luminous Intensity Polar Plot





TEST NUMBER: P684577

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBNH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	377371
5°	368032
10°	339590
15°	300654
20°	261053
25°	223289
30°	184085
35°	121224
40°	65165
45°	28848
50°	11701
55°	8439
60°	5361
65°	3827
70°	3158
75°	2076
80°	3094
85°	0



TEST NUMBER: P684577

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBNH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	619.0	11.5
10°-20°	1476.2	27.5
20°-30°	1691.2	31.5
30°-40°	1136.2	21.2
40°-50°	324.6	6.0
50°-60°	79.5	1.5
60°-70°	30.2	0.6
70°-80°	11.7	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3786.4	70.5
0°-40°	4922.7	91.7
0°-60°	5326.7	99.2
0°-90°	5369.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5369.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6884	
5°	6688	619
15°	5298	1476
25°	3692	1691
35°	1811	1136
45°	372	325
55°	88	79
65°	30	30
75°	10	12
85°	0	1
90°	0	



TEST NUMBER: P684577

CATALOG NUMBER: LX6C75D010 EX6C759035 6LBNH

CANDELA DISTRIBUTION (FULL):

	0°
0°	6883.8
2.5°	6834.9
5°	6687.9
7.5°	6423.4
10°	6100.5
12.5°	5689.0
15°	5297.5
17.5°	4886.3
20°	4474.8
22.5°	4083.3
25°	3691.5
27.5°	3329.2
30°	2908.1
32.5°	2349.9
35°	1811.4
37.5°	1321.8
40°	910.6
42.5°	597.2
45°	372.1
47.5°	225.1
50°	137.2
52.5°	107.6
55°	88.3
57.5°	68.6
60°	48.9
62.5°	39.0
65°	29.5
67.5°	19.7
70°	19.7
72.5°	9.8
75°	9.8
77.5°	9.8
80°	9.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)