

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P856628

Luminaire Tested: **LD6C35D010 EU6359027 6LBWLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P856628  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD6C35D010 EU6359027 6LBWLI  
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBW TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3445.0 lumens  
Efficiency: N/A  
Efficacy: 85.3 lumens/watt  
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P856628

CATALOG NUMBER: LD6C35D010 EU6359027 6LBWLI

### Luminous Intensity Polar Plot





TEST NUMBER: P856628

CATALOG NUMBER: LD6C35D010 EU6359027 6LBWLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	117984
5°	119073
10°	122409
15°	125472
20°	127376
25°	124743
30°	116948
35°	104561
40°	84694
45°	56021
50°	28315
55°	11947
60°	3848
65°	1518
70°	1266
75°	826
80°	0
85°	0



TEST NUMBER: P856628

CATALOG NUMBER: LD6C35D010 EU6359027 6LBWLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	207.6	6.0
10°-20°	624.0	18.1
20°-30°	940.7	27.3
30°-40°	962.8	27.9
40°-50°	560.9	16.3
50°-60°	128.9	3.7
60°-70°	15.8	0.5
70°-80°	4.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1772.4	51.4
0°-40°	2735.2	79.4
0°-60°	3425.0	99.4
0°-90°	3445.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3445.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2152	
5°	2164	208
15°	2211	624
25°	2062	941
35°	1562	963
45°	723	561
55°	125	129
65°	12	16
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P856628

CATALOG NUMBER: LD6C35D010 EU6359027 6LBWLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2152.2
2.5°	2148.2
5°	2163.8
7.5°	2179.4
10°	2199.0
12.5°	2202.9
15°	2210.8
17.5°	2202.9
20°	2183.4
22.5°	2120.9
25°	2062.3
27.5°	1968.6
30°	1847.5
32.5°	1722.5
35°	1562.4
37.5°	1382.6
40°	1183.5
42.5°	960.8
45°	722.6
47.5°	503.8
50°	332.0
52.5°	211.0
55°	125.0
57.5°	66.4
60°	35.1
62.5°	19.5
65°	11.7
67.5°	11.7
70°	7.9
72.5°	3.9
75°	3.9
77.5°	3.9
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)