

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684964

Luminaire Tested: **LX6C35D010 EX6359027 6LBSLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684964
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C35D010 EX6359027 6LBSLI
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBS TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3675.0 lumens
Efficiency: N/A
Efficacy: 91.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684964

CATALOG NUMBER: LX6C35D010 EX6359027 6LBLSI

Luminous Intensity Polar Plot





TEST NUMBER: P684964

CATALOG NUMBER: LX6C35D010 EX6359027 6LBSLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89			89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77			77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68			68
4	88	78	70	64	86	77	69	64	74	68	63	72	67	62	70	65	62	60			60
5	82	71	63	57	80	70	62	57	67	61	56	66	60	55	64	59	55	53			53
6	76	64	56	51	74	63	56	51	62	55	50	60	54	50	59	53	49	47			47
7	71	59	51	46	70	58	51	45	57	50	45	55	49	45	54	49	45	43			43
8	67	54	47	41	65	54	46	41	52	46	41	51	45	41	50	45	41	39			39
9	63	50	43	38	61	50	43	38	49	42	38	48	42	37	47	41	37	36			36
10	59	47	40	35	58	46	39	35	45	39	35	45	39	34	44	38	34	33			33

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	127133
5°	125688
10°	119314
15°	110125
20°	100675
25°	91161
30°	83038
35°	76821
40°	71806
45°	66891
50°	60936
55°	53360
60°	44514
65°	34945
70°	24411
75°	13217
80°	2462
85°	0



TEST NUMBER: P684964

CATALOG NUMBER: LX6C35D010 EX6359027 6LBSLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	213.7	5.8
10°-20°	544.0	14.8
20°-30°	693.8	18.9
30°-40°	719.5	19.6
40°-50°	662.9	18.0
50°-60°	498.7	13.6
60°-70°	269.2	7.3
70°-80°	72.2	2.0
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1451.5	39.5
0°-40°	2171.0	59.1
0°-60°	3332.6	90.7
0°-90°	3675.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3675.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2319	
5°	2284	214
15°	1940	544
25°	1507	694
35°	1148	719
45°	863	663
55°	558	499
65°	269	269
75°	62	72
85°	0	1
90°	0	



TEST NUMBER: P684964

CATALOG NUMBER: LX6C35D010 EX6359027 6LBSLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2319.1
2.5°	2311.3
5°	2284.0
7.5°	2233.2
10°	2143.4
12.5°	2053.6
15°	1940.4
17.5°	1835.0
20°	1725.7
22.5°	1612.5
25°	1507.1
27.5°	1405.6
30°	1311.8
32.5°	1225.9
35°	1147.9
37.5°	1073.7
40°	1003.4
42.5°	929.2
45°	862.8
47.5°	788.7
50°	714.5
52.5°	636.4
55°	558.3
57.5°	480.2
60°	406.0
62.5°	335.7
65°	269.4
67.5°	206.9
70°	152.3
72.5°	105.4
75°	62.4
77.5°	27.3
80°	7.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)