

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685211

Luminaire Tested: **LX6C75D010 EX6759050 6LRMDLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685211
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C75D010 EX6759050 6LRMDLI
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6549.1 lumens
Efficiency: N/A
Efficacy: 80.4 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 81.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685211

CATALOG NUMBER: LX6C75D010 EX6759050 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P685211

CATALOG NUMBER: LX6C75D010 EX6759050 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	536234
5°	537265
10°	512015
15°	440877
20°	363197
25°	283680
30°	204873
35°	104922
40°	51160
45°	21258
50°	3872
55°	2256
60°	1480
65°	1090
70°	801
75°	720
80°	537
85°	0



TEST NUMBER: P685211

CATALOG NUMBER: LX6C75D010 EX6759050 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	915.1	14.0
10°-20°	2153.1	32.9
20°-30°	2132.5	32.6
30°-40°	1081.0	16.5
40°-50°	232.9	3.6
50°-60°	22.2	0.3
60°-70°	8.5	0.1
70°-80°	3.1	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5200.6	79.4
0°-40°	6281.6	95.9
0°-60°	6536.7	99.8
0°-90°	6549.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6549.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9782	
5°	9763	915
15°	7768	2153
25°	4690	2132
35°	1568	1081
45°	274	233
55°	24	22
65°	8	8
75°	3	3
85°	0	1
90°	0	



TEST NUMBER: P685211

CATALOG NUMBER: LX6C75D010 EX6759050 6LRMDLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9781.7
2.5°	9793.5
5°	9763.2
7.5°	9610.2
10°	9198.0
12.5°	8535.3
15°	7768.2
17.5°	6982.6
20°	6225.7
22.5°	5468.7
25°	4689.9
27.5°	3895.9
30°	3236.5
32.5°	2493.0
35°	1567.8
37.5°	1054.7
40°	714.9
42.5°	462.6
45°	274.2
47.5°	122.8
50°	45.4
52.5°	30.3
55°	23.6
57.5°	16.8
60°	13.5
62.5°	10.1
65°	8.4
67.5°	6.7
70°	5.0
72.5°	3.4
75°	3.4
77.5°	1.7
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)