

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684589

Luminaire Tested: **LX6C75D010 EX6C759050 6LBMDH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684589  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C75D010 EX6C759050 6LBMDH  
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6312.0 lumens  
Efficiency: N/A  
Efficacy: 77.4 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684589

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P684589

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62																			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58																			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54																			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	454799
5°	440726
10°	405832
15°	364003
20°	323877
25°	268957
30°	192156
35°	123520
40°	75270
45°	41842
50°	18541
55°	10743
60°	7072
65°	5020
70°	3542
75°	2732
80°	1736
85°	1132



TEST NUMBER: P684589

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	741.3	11.7
10°-20°	1794.4	28.4
20°-30°	1995.5	31.6
30°-40°	1182.4	18.7
40°-50°	433.2	6.9
50°-60°	108.9	1.7
60°-70°	39.7	0.6
70°-80°	13.8	0.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4531.3	71.8
0°-40°	5713.7	90.5
0°-60°	6255.7	99.1
0°-90°	6312.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6312.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8296	
5°	8009	741
15°	6414	1794
25°	4446	1996
35°	1846	1182
45°	540	433
55°	112	109
65°	39	40
75°	13	14
85°	2	3
90°	0	



TEST NUMBER: P684589

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	8296.2
2.5°	8222.5
5°	8008.9
7.5°	7684.7
10°	7290.5
12.5°	6855.8
15°	6413.7
17.5°	5984.5
20°	5551.7
22.5°	5048.8
25°	4446.5
27.5°	3753.9
30°	3035.6
32.5°	2392.7
35°	1845.7
37.5°	1401.7
40°	1051.8
42.5°	766.3
45°	539.7
47.5°	342.6
50°	217.4
52.5°	152.9
55°	112.4
57.5°	84.7
60°	64.5
62.5°	49.7
65°	38.7
67.5°	29.5
70°	22.1
72.5°	16.6
75°	12.9
77.5°	9.2
80°	5.5
82.5°	3.7
85°	1.8
87.5°	1.8
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)