

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684976

Luminaire Tested: **LX6C35D010 EX6359035 6LRMDLI**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P684976  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C35D010 EX6359035 6LRMDLI  
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2697.0 lumens  
Efficiency: N/A  
Efficacy: 66.8 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 40.4  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684976

CATALOG NUMBER: LX6C35D010 EX6359035 6LRMDLI

### Luminous Intensity Polar Plot





TEST NUMBER: P684976

CATALOG NUMBER: LX6C35D010 EX6359035 6LRMDLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	220832
5°	221257
10°	210857
15°	181562
20°	149568
25°	116825
30°	84367
35°	43206
40°	21068
45°	8753
50°	1595
55°	927
60°	603
65°	454
70°	337
75°	297
80°	221
85°	0



TEST NUMBER: P684976

CATALOG NUMBER: LX6C35D010 EX6359035 6LRMDLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	376.9	14.0
10°-20°	886.7	32.9
20°-30°	878.2	32.6
30°-40°	445.2	16.5
40°-50°	95.9	3.6
50°-60°	9.1	0.3
60°-70°	3.5	0.1
70°-80°	1.3	0.0
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2141.7	79.4
0°-40°	2586.9	95.9
0°-60°	2691.9	99.8
0°-90°	2697.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2697.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4028	
5°	4021	377
15°	3199	887
25°	1931	878
35°	646	445
45°	113	96
55°	10	9
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P684976

CATALOG NUMBER: LX6C35D010 EX6359035 6LRMDLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	4028.3
2.5°	4033.2
5°	4020.7
7.5°	3957.6
10°	3787.9
12.5°	3515.0
15°	3199.1
17.5°	2875.6
20°	2563.8
22.5°	2252.1
25°	1931.4
27.5°	1604.4
30°	1332.8
32.5°	1026.6
35°	645.6
37.5°	434.4
40°	294.4
42.5°	190.5
45°	112.9
47.5°	50.6
50°	18.7
52.5°	12.5
55°	9.7
57.5°	6.9
60°	5.5
62.5°	4.2
65°	3.5
67.5°	2.8
70°	2.1
72.5°	1.4
75°	1.4
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)