

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684592

Luminaire Tested: **LX6C75D010 EX6C759050 6LBSH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684592  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C75D010 EX6C759050 6LBSH  
Description: 6 INCH 7500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9090.0 lumens  
Efficiency: N/A  
Efficacy: 111.5 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 81.5  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684592

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684592

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	260621
5°	259404
10°	254048
15°	244814
20°	233552
25°	220966
30°	208431
35°	196259
40°	184789
45°	172258
50°	157061
55°	138710
60°	117414
65°	92189
70°	65780
75°	36029
80°	6346
85°	0



TEST NUMBER: P684592

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	445.3	4.9
10°-20°	1210.3	13.3
20°-30°	1680.8	18.5
30°-40°	1834.2	20.2
40°-50°	1711.0	18.8
50°-60°	1298.7	14.3
60°-70°	711.1	7.8
70°-80°	195.7	2.2
80°-90°	2.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3336.4	36.7
0°-40°	5170.7	56.9
0°-60°	8180.4	90.0
0°-90°	9090.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9090.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4754	
5°	4714	445
15°	4314	1210
25°	3653	1681
35°	2933	1834
45°	2222	1711
55°	1451	1299
65°	711	711
75°	170	196
85°	0	3
90°	0	



TEST NUMBER: P684592

CATALOG NUMBER: LX6C75D010 EX6C759050 6LBSH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4754.1
2.5°	4754.1
5°	4713.9
7.5°	4653.8
10°	4563.8
12.5°	4443.7
15°	4313.6
17.5°	4153.5
20°	4003.4
22.5°	3823.2
25°	3653.1
27.5°	3482.9
30°	3292.7
32.5°	3112.5
35°	2932.6
37.5°	2752.4
40°	2582.2
42.5°	2402.0
45°	2221.9
47.5°	2041.7
50°	1841.6
52.5°	1651.4
55°	1451.3
57.5°	1261.1
60°	1070.9
62.5°	880.8
65°	710.7
67.5°	550.4
70°	410.4
72.5°	280.2
75°	170.1
77.5°	80.2
80°	20.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)