

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684227

Luminaire Tested: **LX6C35D010 EX6C359035 6LBSH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684227
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C35D010 EX6C359035 6LBSH
Description: 6 INCH 3500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3743.0 lumens
Efficiency: N/A
Efficacy: 92.6 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 40.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684227

CATALOG NUMBER: LX6C35D010 EX6C359035 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684227

CATALOG NUMBER: LX6C35D010 EX6C359035 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	107316
5°	106812
10°	104613
15°	100806
20°	96171
25°	90985
30°	85823
35°	80810
40°	76093
45°	70930
50°	64672
55°	57116
60°	48340
65°	37955
70°	27088
75°	14848
80°	2620
85°	0



TEST NUMBER: P684227

CATALOG NUMBER: LX6C35D010 EX6C359035 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	4.9
10°-20°	498.4	13.3
20°-30°	692.1	18.5
30°-40°	755.3	20.2
40°-50°	704.6	18.8
50°-60°	534.8	14.3
60°-70°	292.8	7.8
70°-80°	80.6	2.2
80°-90°	1.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1373.8	36.7
0°-40°	2129.1	56.9
0°-60°	3368.4	90.0
0°-90°	3743.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3743.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1958	
5°	1941	183
15°	1776	498
25°	1504	692
35°	1208	755
45°	915	705
55°	598	535
65°	293	293
75°	70	81
85°	0	1
90°	0	



TEST NUMBER: P684227

CATALOG NUMBER: LX6C35D010 EX6C359035 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1957.6
2.5°	1957.6
5°	1941.0
7.5°	1916.3
10°	1879.3
12.5°	1829.8
15°	1776.2
17.5°	1710.3
20°	1648.5
22.5°	1574.3
25°	1504.2
27.5°	1434.2
30°	1355.8
32.5°	1281.6
35°	1207.5
37.5°	1133.3
40°	1063.3
42.5°	989.1
45°	914.9
47.5°	840.7
50°	758.3
52.5°	680.0
55°	597.6
57.5°	519.3
60°	440.9
62.5°	362.7
65°	292.6
67.5°	226.6
70°	169.0
72.5°	115.4
75°	70.1
77.5°	33.0
80°	8.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)