

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685218

Luminaire Tested: **LX6C08D010 EX6089030 6LBNLI**

Issue Date: 2/14/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P685218  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6089030 6LBNLI  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 715.0 lumens  
Efficiency: N/A  
Efficacy: 72.2 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685218

CATALOG NUMBER: LX6C08D010 EX6089030 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685218

CATALOG NUMBER: LX6C08D010 EX6089030 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	89242
5°	83458
10°	68063
15°	50085
20°	34525
25°	25628
30°	19250
35°	12006
40°	5825
45°	2000
50°	264
55°	201
60°	110
65°	130
70°	160
75°	0
80°	0
85°	0



TEST NUMBER: P685218

CATALOG NUMBER: LX6C08D010 EX6089030 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	135.3	18.9
10°-20°	242.9	34.0
20°-30°	196.4	27.5
30°-40°	113.1	15.8
40°-50°	23.9	3.3
50°-60°	2.1	0.3
60°-70°	1.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	574.7	80.4
0°-40°	687.9	96.2
0°-60°	713.9	99.8
0°-90°	715.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	715.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1628	
5°	1517	135
15°	882	243
25°	424	196
35°	179	113
45°	26	24
55°	2	2
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P685218

CATALOG NUMBER: LX6C08D010 EX6089030 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1627.9
2.5°	1608.3
5°	1516.6
7.5°	1384.6
10°	1222.7
12.5°	1056.8
15°	882.5
17.5°	714.5
20°	591.8
22.5°	498.0
25°	423.7
27.5°	360.8
30°	304.1
32.5°	241.3
35°	179.4
37.5°	124.7
40°	81.4
42.5°	49.5
45°	25.8
47.5°	10.3
50°	3.1
52.5°	3.1
55°	2.1
57.5°	2.1
60°	1.0
62.5°	1.0
65°	1.0
67.5°	1.0
70°	1.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)