

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684611

Luminaire Tested: **LX6C08D010 EX6C089030 6LBWH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P684611
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C08D010 EX6C089030 6LBWH
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LBW TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 795.0 lumens
Efficiency: N/A
Efficacy: 80.3 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684611

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

Luminous Intensity Polar Plot





TEST NUMBER: P684611

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26878
5°	26871
10°	26664
15°	26487
20°	26083
25°	25483
30°	23997
35°	21717
40°	18134
45°	13893
50°	9842
55°	6203
60°	3498
65°	2270
70°	1491
75°	1080
80°	663
85°	629



TEST NUMBER: P684611

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.3	5.8
10°-20°	131.4	16.5
20°-30°	192.7	24.2
30°-40°	200.5	25.2
40°-50°	138.7	17.5
50°-60°	60.4	7.6
60°-70°	18.5	2.3
70°-80°	5.6	0.7
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.4	46.6
0°-40°	570.9	71.8
0°-60°	770.1	96.9
0°-90°	795.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	795.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	490	
5°	488	46
15°	467	131
25°	421	193
35°	324	201
45°	179	139
55°	65	60
65°	18	19
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P684611

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBWH

CANDELA DISTRIBUTION (FULL):

	0°
0°	490.3
2.5°	491.4
5°	488.3
7.5°	484.2
10°	479.0
12.5°	473.8
15°	466.7
17.5°	457.4
20°	447.1
22.5°	435.7
25°	421.3
27.5°	402.8
30°	379.1
32.5°	354.3
35°	324.5
37.5°	291.5
40°	253.4
42.5°	215.3
45°	179.2
47.5°	145.2
50°	115.4
52.5°	87.6
55°	64.9
57.5°	46.4
60°	31.9
62.5°	23.7
65°	17.5
67.5°	13.4
70°	9.3
72.5°	7.2
75°	5.1
77.5°	3.1
80°	2.1
82.5°	1.0
85°	1.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)