

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685224

Luminaire Tested: **LX6C08D010 EX6089035 6LBSLI**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P685224  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205419)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6089035 6LBSLI  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND 6LBS TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 983.0 lumens  
Efficiency: N/A  
Efficacy: 99.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 1.04  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685224

CATALOG NUMBER: LX6C08D010 EX6089035 6LBSLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685224

CATALOG NUMBER: LX6C08D010 EX6089035 6LBSLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 111 | 107 | 104 | 101 | 109 | 105 | 102 | 99  | 101 | 99  | 96  | 97  | 95  | 93  | 94  | 92  | 91  | 89  | 89  | 89  | 89  |
| 2   | 103 | 96  | 91  | 86  | 100 | 94  | 89  | 85  | 91  | 87  | 83  | 88  | 84  | 81  | 85  | 82  | 79  | 77  | 77  | 77  | 77  |
| 3   | 95  | 86  | 79  | 74  | 93  | 85  | 78  | 73  | 82  | 76  | 72  | 79  | 75  | 71  | 77  | 73  | 70  | 68  | 68  | 68  | 68  |
| 4   | 88  | 78  | 70  | 64  | 86  | 77  | 69  | 64  | 74  | 68  | 63  | 72  | 67  | 62  | 70  | 65  | 62  | 60  | 60  | 60  | 60  |
| 5   | 82  | 71  | 63  | 57  | 80  | 70  | 62  | 57  | 67  | 61  | 56  | 66  | 60  | 55  | 64  | 59  | 55  | 53  | 53  | 53  | 53  |
| 6   | 76  | 64  | 56  | 51  | 74  | 63  | 56  | 51  | 62  | 55  | 50  | 60  | 54  | 50  | 59  | 53  | 49  | 47  | 47  | 47  | 47  |
| 7   | 71  | 59  | 51  | 46  | 70  | 58  | 51  | 45  | 57  | 50  | 45  | 55  | 49  | 45  | 54  | 49  | 45  | 43  | 43  | 43  | 43  |
| 8   | 67  | 54  | 47  | 41  | 65  | 54  | 46  | 41  | 52  | 46  | 41  | 51  | 45  | 41  | 50  | 45  | 41  | 39  | 39  | 39  | 39  |
| 9   | 63  | 50  | 43  | 38  | 61  | 50  | 43  | 38  | 49  | 42  | 38  | 48  | 42  | 37  | 47  | 41  | 37  | 36  | 36  | 36  | 36  |
| 10  | 59  | 47  | 40  | 35  | 58  | 46  | 39  | 35  | 45  | 39  | 35  | 45  | 39  | 34  | 44  | 38  | 34  | 33  | 33  | 33  | 33  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |       |
|-----|-------|
|     | 0°    |
| 0°  | 34005 |
| 5°  | 33618 |
| 10° | 31913 |
| 15° | 29455 |
| 20° | 26929 |
| 25° | 24382 |
| 30° | 22212 |
| 35° | 20545 |
| 40° | 19207 |
| 45° | 17893 |
| 50° | 16298 |
| 55° | 14270 |
| 60° | 11907 |
| 65° | 9352  |
| 70° | 6524  |
| 75° | 3537  |
| 80° | 663   |
| 85° | 0     |



TEST NUMBER: P685224

CATALOG NUMBER: LX6C08D010 EX6089035 6LBSLI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 57.2   | 5.8       |
| 10°-20°   | 145.5  | 14.8      |
| 20°-30°   | 185.6  | 18.9      |
| 30°-40°   | 192.4  | 19.6      |
| 40°-50°   | 177.3  | 18.0      |
| 50°-60°   | 133.4  | 13.6      |
| 60°-70°   | 72.0   | 7.3       |
| 70°-80°   | 19.3   | 2.0       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 388.2  | 39.5      |
| 0°-40°    | 580.7  | 59.1      |
| 0°-60°    | 891.4  | 90.7      |
| 0°-90°    | 983.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 983.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 620 |      |
| 5°  | 611 | 57   |
| 15° | 519 | 146  |
| 25° | 403 | 186  |
| 35° | 307 | 192  |
| 45° | 231 | 177  |
| 55° | 149 | 133  |
| 65° | 72  | 72   |
| 75° | 17  | 19   |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P685224

CATALOG NUMBER: LX6C08D010 EX6089035 6LBSLI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°    |
|-------|-------|
| 0°    | 620.3 |
| 2.5°  | 618.2 |
| 5°    | 610.9 |
| 7.5°  | 597.3 |
| 10°   | 573.3 |
| 12.5° | 549.3 |
| 15°   | 519.0 |
| 17.5° | 490.8 |
| 20°   | 461.6 |
| 22.5° | 431.3 |
| 25°   | 403.1 |
| 27.5° | 376.0 |
| 30°   | 350.9 |
| 32.5° | 327.9 |
| 35°   | 307.0 |
| 37.5° | 287.2 |
| 40°   | 268.4 |
| 42.5° | 248.6 |
| 45°   | 230.8 |
| 47.5° | 211.0 |
| 50°   | 191.1 |
| 52.5° | 170.2 |
| 55°   | 149.3 |
| 57.5° | 128.5 |
| 60°   | 108.6 |
| 62.5° | 89.8  |
| 65°   | 72.1  |
| 67.5° | 55.4  |
| 70°   | 40.7  |
| 72.5° | 28.2  |
| 75°   | 16.7  |
| 77.5° | 7.3   |
| 80°   | 2.1   |
| 82.5° | 0.0   |
| 85°   | 0.0   |
| 87.5° | 0.0   |
| 90°   | 0.0   |



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)