

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684632

Luminaire Tested: **LX6C08D010 EX6C089050 6LBWH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P684632  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6C089050 6LBWH  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND 6LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 824.0 lumens  
Efficiency: N/A  
Efficacy: 83.2 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684632

CATALOG NUMBER: LX6C08D010 EX6C089050 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P684632

CATALOG NUMBER: LX6C08D010 EX6C089050 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27860
5°	27850
10°	27638
15°	27452
20°	27034
25°	26415
30°	24871
35°	22506
40°	18792
45°	14405
50°	10200
55°	6432
60°	3629
65°	2361
70°	1539
75°	1123
80°	663
85°	692



TEST NUMBER: P684632

CATALOG NUMBER: LX6C08D010 EX6C089050 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	48.0	5.8
10°-20°	136.2	16.5
20°-30°	199.7	24.2
30°-40°	207.8	25.2
40°-50°	143.8	17.5
50°-60°	62.6	7.6
60°-70°	19.2	2.3
70°-80°	5.7	0.7
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	383.9	46.6
0°-40°	591.8	71.8
0°-60°	798.2	96.9
0°-90°	824.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	824.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	508	
5°	506	48
15°	484	136
25°	437	200
35°	336	208
45°	186	144
55°	67	63
65°	18	19
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P684632

CATALOG NUMBER: LX6C08D010 EX6C089050 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	508.2
2.5°	509.3
5°	506.1
7.5°	501.8
10°	496.5
12.5°	491.1
15°	483.7
17.5°	474.1
20°	463.4
22.5°	451.6
25°	436.7
27.5°	417.5
30°	392.9
32.5°	367.3
35°	336.3
37.5°	302.2
40°	262.6
42.5°	223.2
45°	185.8
47.5°	150.5
50°	119.6
52.5°	90.8
55°	67.3
57.5°	48.1
60°	33.1
62.5°	24.6
65°	18.2
67.5°	13.9
70°	9.6
72.5°	7.5
75°	5.3
77.5°	3.2
80°	2.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)