

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563942

Luminaire Tested: **LX6C40D010 EX6C409030 6LBMH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P563942
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C40D010 EX6C409030 6LBMH
Description: 6 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3058.7 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563942

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMH

Luminous Intensity Polar Plot





TEST NUMBER: P563942

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	165946
5°	162976
10°	154651
15°	145018
20°	135053
25°	124441
30°	103687
35°	73080
40°	46573
45°	27778
50°	16400
55°	10427
60°	7181
65°	5098
70°	3510
75°	2775
80°	1357
85°	0



TEST NUMBER: P563942

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.8	9.0
10°-20°	716.0	23.4
20°-30°	927.7	30.3
30°-40°	688.8	22.5
40°-50°	290.8	9.5
50°-60°	103.2	3.4
60°-70°	39.8	1.3
70°-80°	13.8	0.5
80°-90°	1.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1920.5	62.8
0°-40°	2609.3	85.3
0°-60°	3003.3	98.2
0°-90°	3058.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3058.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3027	
5°	2962	277
15°	2555	716
25°	2057	928
35°	1092	689
45°	358	291
55°	109	103
65°	39	40
75°	13	14
85°	0	2
90°	0	



TEST NUMBER: P563942

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3027.1
2.5°	3018.2
5°	2961.6
7.5°	2878.5
10°	2778.2
12.5°	2668.8
15°	2555.2
17.5°	2428.7
20°	2315.0
22.5°	2197.2
25°	2057.3
27.5°	1865.0
30°	1638.0
32.5°	1371.5
35°	1092.0
37.5°	856.2
40°	650.8
42.5°	484.8
45°	358.3
47.5°	262.0
50°	192.3
52.5°	144.1
55°	109.1
57.5°	82.9
60°	65.5
62.5°	48.1
65°	39.3
67.5°	30.5
70°	21.9
72.5°	17.4
75°	13.1
77.5°	8.7
80°	4.3
82.5°	4.3
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)