

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684636

Luminaire Tested: **LX6C08D010 EX6C089730 6LBSH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P684636  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C08D010 EX6C089730 6LBSH  
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 97CRI LEDS AND 6LBS TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.   Condition   Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 936.0 lumens  
Efficiency: N/A  
Efficacy: 94.6 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 9.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684636

CATALOG NUMBER: LX6C08D010 EX6C089730 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P684636

CATALOG NUMBER: LX6C08D010 EX6C089730 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77																			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67																			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58																			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51																			
6	75	63	55	49	73	62	54	49	60	54	48	59	53	48	57	52	48	46																			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41																			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37																			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34																			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26834
5°	26711
10°	26157
15°	25210
20°	24047
25°	22755
30°	21465
35°	20211
40°	19029
45°	17738
50°	16170
55°	14279
60°	12093
65°	9495
70°	6780
75°	3707
80°	663
85°	0



TEST NUMBER: P684636

CATALOG NUMBER: LX6C08D010 EX6C089730 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	45.9	4.9
10°-20°	124.6	13.3
20°-30°	173.1	18.5
30°-40°	188.9	20.2
40°-50°	176.2	18.8
50°-60°	133.7	14.3
60°-70°	73.2	7.8
70°-80°	20.2	2.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	343.6	36.7
0°-40°	532.4	56.9
0°-60°	842.3	90.0
0°-90°	936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	490	
5°	485	46
15°	444	125
25°	376	173
35°	302	189
45°	229	176
55°	149	134
65°	73	73
75°	18	20
85°	0	0
90°	0	



TEST NUMBER: P684636

CATALOG NUMBER: LX6C08D010 EX6C089730 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	489.5
2.5°	489.5
5°	485.4
7.5°	479.2
10°	469.9
12.5°	457.6
15°	444.2
17.5°	427.7
20°	412.2
22.5°	393.7
25°	376.2
27.5°	358.6
30°	339.1
32.5°	320.5
35°	302.0
37.5°	283.4
40°	265.9
42.5°	247.3
45°	228.8
47.5°	210.2
50°	189.6
52.5°	170.0
55°	149.4
57.5°	129.9
60°	110.3
62.5°	90.7
65°	73.2
67.5°	56.7
70°	42.3
72.5°	28.9
75°	17.5
77.5°	8.3
80°	2.1
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)