

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563944

Luminaire Tested: **LX6C40D010 EX6C409030 6LBSH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P563944  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C40D010 EX6C409030 6LBSH  
Description: 6 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBS TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4357.8 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563944

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBSH

### Luminous Intensity Polar Plot





TEST NUMBER: P563944

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBSH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	124935
5°	124356
10°	121791
15°	117362
20°	111969
25°	105932
30°	99920
35°	94087
40°	88587
45°	82574
50°	75290
55°	66502
60°	56289
65°	44194
70°	31528
75°	17284
80°	3062
85°	0



TEST NUMBER: P563944

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBSH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	213.5	4.9
10°-20°	580.2	13.3
20°-30°	805.8	18.5
30°-40°	879.3	20.2
40°-50°	820.2	18.8
50°-60°	622.6	14.3
60°-70°	340.9	7.8
70°-80°	93.9	2.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1599.5	36.7
0°-40°	2478.8	56.9
0°-60°	3921.7	90.0
0°-90°	4357.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4357.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2279	
5°	2260	213
15°	2068	580
25°	1751	806
35°	1406	879
45°	1065	820
55°	696	623
65°	341	341
75°	82	94
85°	0	1
90°	0	



TEST NUMBER: P563944

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBSH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2279.0
2.5°	2279.0
5°	2259.8
7.5°	2231.0
10°	2187.9
12.5°	2130.3
15°	2067.9
17.5°	1991.2
20°	1919.3
22.5°	1832.8
25°	1751.3
27.5°	1669.7
30°	1578.5
32.5°	1492.1
35°	1405.9
37.5°	1319.5
40°	1237.9
42.5°	1151.6
45°	1065.1
47.5°	978.7
50°	882.8
52.5°	791.7
55°	695.8
57.5°	604.5
60°	513.4
62.5°	422.2
65°	340.7
67.5°	263.9
70°	196.7
72.5°	134.4
75°	81.6
77.5°	38.5
80°	9.7
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)