

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563945

Luminaire Tested: **LX6C40D010 EX6C409030 6LBWH**

Issue Date: 2/15/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P563945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C40D010 EX6C409030 6LBWH  
Description: 6 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LBW TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3701.6 lumens  
Efficiency: N/A  
Efficacy: 78.8 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 47  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563945

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P563945

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	125154
5°	125110
10°	124146
15°	123315
20°	121437
25°	118664
30°	111726
35°	101114
40°	84437
45°	64697
50°	45824
55°	28883
60°	16293
65°	10585
70°	6908
75°	5083
80°	3062
85°	3019



TEST NUMBER: P563945

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	215.6	5.8
10°-20°	611.9	16.5
20°-30°	897.1	24.2
30°-40°	933.7	25.2
40°-50°	646.0	17.5
50°-60°	281.2	7.6
60°-70°	86.3	2.3
70°-80°	25.9	0.7
80°-90°	3.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1724.6	46.6
0°-40°	2658.3	71.8
0°-60°	3585.5	96.9
0°-90°	3701.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3701.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2283	
5°	2274	216
15°	2173	612
25°	1962	897
35°	1511	934
45°	834	646
55°	302	281
65°	82	86
75°	24	26
85°	5	4
90°	0	



TEST NUMBER: P563945

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2283.0
2.5°	2287.8
5°	2273.5
7.5°	2254.4
10°	2230.2
12.5°	2206.3
15°	2172.8
17.5°	2129.5
20°	2081.6
22.5°	2028.9
25°	1961.8
27.5°	1875.4
30°	1765.0
32.5°	1649.9
35°	1510.9
37.5°	1357.5
40°	1179.9
42.5°	1002.5
45°	834.5
47.5°	676.2
50°	537.3
52.5°	407.8
55°	302.2
57.5°	215.8
60°	148.6
62.5°	110.4
65°	81.6
67.5°	62.5
70°	43.1
72.5°	33.7
75°	24.0
77.5°	14.3
80°	9.7
82.5°	4.8
85°	4.8
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)