

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563983

Luminaire Tested: **LX6C08D010 EX6C089030 6LBMDH**

Issue Date: 2/15/2022

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



Test Information

Test Method: LM-79-08
Report Number: P563983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C08D010 EX6C089030 6LBMDH
Description: 6 INCH 800 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LRMD45 TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Luminaire Equipment: Sample No. Condition Description

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 650.0 lumens
Efficiency: N/A
Efficacy: 65.7 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563983

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P563983

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46833
5°	45383
10°	41794
15°	37486
20°	33352
25°	27697
30°	19788
35°	12722
40°	7750
45°	4311
50°	1910
55°	1109
60°	724
65°	519
70°	369
75°	275
80°	189
85°	126



TEST NUMBER: P563983

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	11.7
10°-20°	184.8	28.4
20°-30°	205.5	31.6
30°-40°	121.8	18.7
40°-50°	44.6	6.9
50°-60°	11.2	1.7
60°-70°	4.1	0.6
70°-80°	1.4	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.6	71.8
0°-40°	588.4	90.5
0°-60°	644.2	99.1
0°-90°	650.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	650.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	854	
5°	825	76
15°	660	185
25°	458	205
35°	190	122
45°	56	45
55°	12	11
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P563983

CATALOG NUMBER: LX6C08D010 EX6C089030 6LBMDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	854.3
2.5°	846.7
5°	824.7
7.5°	791.4
10°	750.8
12.5°	706.0
15°	660.5
17.5°	616.3
20°	571.7
22.5°	519.9
25°	457.9
27.5°	386.6
30°	312.6
32.5°	246.4
35°	190.1
37.5°	144.3
40°	108.3
42.5°	78.9
45°	55.6
47.5°	35.3
50°	22.4
52.5°	15.7
55°	11.6
57.5°	8.7
60°	6.6
62.5°	5.1
65°	4.0
67.5°	3.0
70°	2.3
72.5°	1.7
75°	1.3
77.5°	0.9
80°	0.6
82.5°	0.4
85°	0.2
87.5°	0.2
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)