

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563941

Luminaire Tested: **LX6C40D010 EX6C409030 6LBMDH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563941
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C40D010 EX6C409030 6LBMDH
Description: 6 INCH 4000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LRMD45 TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2975.0 lumens
Efficiency: N/A
Efficacy: 63.3 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 47
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563941

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P563941

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	214358
5°	207726
10°	191279
15°	171562
20°	152648
25°	126763
30°	90565
35°	58216
40°	35474
45°	19723
50°	8733
55°	5066
60°	3333
65°	2361
70°	1667
75°	1292
80°	821
85°	566



TEST NUMBER: P563941

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	349.4	11.7
10°-20°	845.7	28.4
20°-30°	940.5	31.6
30°-40°	557.3	18.7
40°-50°	204.2	6.9
50°-60°	51.3	1.7
60°-70°	18.7	0.6
70°-80°	6.5	0.2
80°-90°	1.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2135.7	71.8
0°-40°	2693.0	90.5
0°-60°	2948.5	99.1
0°-90°	2975.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2975.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3910	
5°	3775	349
15°	3023	846
25°	2096	941
35°	870	557
45°	254	204
55°	53	51
65°	18	19
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P563941

CATALOG NUMBER: LX6C40D010 EX6C409030 6LBMDH

CANDELA DISTRIBUTION (FULL):

	0°
0°	3910.2
2.5°	3875.5
5°	3774.8
7.5°	3622.0
10°	3436.2
12.5°	3231.3
15°	3022.9
17.5°	2820.7
20°	2616.6
22.5°	2379.6
25°	2095.7
27.5°	1769.3
30°	1430.7
32.5°	1127.7
35°	869.9
37.5°	660.7
40°	495.7
42.5°	361.2
45°	254.4
47.5°	161.5
50°	102.4
52.5°	72.1
55°	53.0
57.5°	39.9
60°	30.4
62.5°	23.4
65°	18.2
67.5°	13.9
70°	10.4
72.5°	7.8
75°	6.1
77.5°	4.3
80°	2.6
82.5°	1.7
85°	0.9
87.5°	0.9
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)