

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685237

Luminaire Tested: **LX6C80D010 EX6809027 6LBMLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685237
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C80D010 EX6809027 6LBMLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7827.0 lumens
Efficiency: N/A
Efficacy: 87.5 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685237
CATALOG NUMBER: LX6C80D010 EX6809027 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685237

CATALOG NUMBER: LX6C80D010 EX6809027 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94																			
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82																			
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76																			
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	536969
5°	531861
10°	503988
15°	457574
20°	404332
25°	349556
30°	273245
35°	167569
40°	86011
45°	34166
50°	11096
55°	3823
60°	3278
65°	2620
70°	1619
75°	2139
80°	0
85°	0



TEST NUMBER: P685237

CATALOG NUMBER: LX6C80D010 EX6809027 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	902.3	11.5
10°-20°	2246.5	28.7
20°-30°	2611.5	33.4
30°-40°	1599.2	20.4
40°-50°	397.1	5.1
50°-60°	46.4	0.6
60°-70°	17.4	0.2
70°-80°	6.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5760.3	73.6
0°-40°	7359.5	94.0
0°-60°	7803.0	99.7
0°-90°	7827.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7827.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9795	
5°	9665	902
15°	8062	2247
25°	5779	2611
35°	2504	1599
45°	441	397
55°	40	46
65°	20	17
75°	10	7
85°	0	0
90°	0	



TEST NUMBER: P685237

CATALOG NUMBER: LX6C80D010 EX6809027 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9795.1
2.5°	9785.0
5°	9665.0
7.5°	9404.5
10°	9053.8
12.5°	8593.2
15°	8062.4
17.5°	7491.6
20°	6930.8
22.5°	6369.7
25°	5779.0
27.5°	5097.9
30°	4316.6
32.5°	3405.2
35°	2503.9
37.5°	1762.6
40°	1201.9
42.5°	751.0
45°	440.7
47.5°	250.5
50°	130.1
52.5°	60.2
55°	40.0
57.5°	29.9
60°	29.9
62.5°	20.2
65°	20.2
67.5°	10.1
70°	10.1
72.5°	10.1
75°	10.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)