

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684291

Luminaire Tested: **LX6C45D010 EX6C459027 6LBSH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P684291
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C45D010 EX6C459027 6LBSH
Description: 6 INCH 4500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4771.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 49.6
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684291

CATALOG NUMBER: LX6C45D010 EX6C459027 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684291

CATALOG NUMBER: LX6C45D010 EX6C459027 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	111	107	104	101	108	105	102	99	101	98	96	97	95	93	93	92	90	88			
2	102	96	90	85	100	94	88	84	90	86	82	87	83	80	84	81	79	77			
3	95	85	78	73	92	84	77	72	81	75	71	78	74	70	76	72	69	67			
4	87	77	69	63	85	75	68	63	73	67	62	71	65	61	69	64	60	58			
5	81	69	61	55	79	68	61	55	66	60	55	64	59	54	63	58	53	51			
6	75	63	55	49	73	62	54	49	60	54	49	59	53	48	57	52	48	46			
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41			
8	65	53	45	40	64	52	45	40	51	44	39	50	44	39	49	43	39	37			
9	61	49	41	36	60	48	41	36	47	40	36	46	40	36	45	40	35	34			
10	58	45	38	33	56	45	38	33	44	37	33	43	37	33	42	37	33	31			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	136787
5°	136149
10°	133342
15°	128491
20°	122581
25°	115978
30°	109397
35°	103008
40°	96989
45°	90412
50°	82437
55°	72800
60°	61629
65°	48384
70°	34525
75°	18915
80°	3315
85°	0



TEST NUMBER: P684291

CATALOG NUMBER: LX6C45D010 EX6C459027 6LBSH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	233.7	4.9
10°-20°	635.2	13.3
20°-30°	882.2	18.5
30°-40°	962.7	20.2
40°-50°	898.1	18.8
50°-60°	681.6	14.3
60°-70°	373.3	7.8
70°-80°	102.7	2.2
80°-90°	1.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1751.2	36.7
0°-40°	2713.9	56.9
0°-60°	4293.6	90.0
0°-90°	4771.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4771.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2495	
5°	2474	234
15°	2264	635
25°	1917	882
35°	1539	963
45°	1166	898
55°	762	682
65°	373	373
75°	89	103
85°	0	1
90°	0	



TEST NUMBER: P684291

CATALOG NUMBER: LX6C45D010 EX6C459027 6LBSH

CANDELA DISTRIBUTION (FULL):

	0°
0°	2495.2
2.5°	2495.2
5°	2474.1
7.5°	2442.6
10°	2395.4
12.5°	2332.3
15°	2264.0
17.5°	2180.0
20°	2101.2
22.5°	2006.7
25°	1917.4
27.5°	1828.1
30°	1728.2
32.5°	1633.6
35°	1539.2
37.5°	1444.6
40°	1355.3
42.5°	1260.7
45°	1166.2
47.5°	1071.6
50°	966.6
52.5°	866.7
55°	761.7
57.5°	661.9
60°	562.1
62.5°	462.3
65°	373.0
67.5°	288.9
70°	215.4
72.5°	147.1
75°	89.3
77.5°	42.1
80°	10.5
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)