

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685243

Luminaire Tested: **LX6C80D010 EX6809030 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685243
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C80D010 EX6809030 6LBNLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7231.0 lumens
Efficiency: N/A
Efficacy: 80.8 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685243

CATALOG NUMBER: LX6C80D010 EX6809030 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685243

CATALOG NUMBER: LX6C80D010 EX6809030 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	902521
5°	844011
10°	688353
15°	506541
20°	349138
25°	259200
30°	194695
35°	121412
40°	58932
45°	20219
50°	2652
55°	2007
60°	1151
65°	1362
70°	1683
75°	0
80°	0
85°	0



TEST NUMBER: P685243

CATALOG NUMBER: LX6C80D010 EX6809030 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1368.8	18.9
10°-20°	2456.9	34.0
20°-30°	1986.4	27.5
30°-40°	1144.3	15.8
40°-50°	241.9	3.3
50°-60°	20.9	0.3
60°-70°	10.4	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5812.1	80.4
0°-40°	6956.4	96.2
0°-60°	7219.2	99.8
0°-90°	7231.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7231.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	16463	
5°	15337	###
15°	8925	2457
25°	4285	1986
35°	1814	1144
45°	261	242
55°	21	21
65°	10	10
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685243

CATALOG NUMBER: LX6C80D010 EX6809030 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	16463.3
2.5°	16265.4
5°	15337.4
7.5°	14002.8
10°	12365.8
12.5°	10687.3
15°	8925.2
17.5°	7225.6
20°	5984.7
22.5°	5036.0
25°	4285.2
27.5°	3649.3
30°	3075.7
32.5°	2439.9
35°	1814.2
37.5°	1261.5
40°	823.5
42.5°	500.6
45°	260.8
47.5°	104.2
50°	31.1
52.5°	31.1
55°	21.0
57.5°	21.0
60°	10.5
62.5°	10.5
65°	10.5
67.5°	10.5
70°	10.5
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)