

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685251

Luminaire Tested: **LX6C80D010 EX6809035 6LRMDLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685251
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-20)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C80D010 EX6809035 6LRMDLI
Description: 6 INCH 8000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3500K, 90CRI LEDS
AND 6LRMD45 TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6921.1 lumens
Efficiency: N/A
Efficacy: 77.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.77
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 89.5
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685251

CATALOG NUMBER: LX6C80D010 EX6809035 6LRMDLI

Luminous Intensity Polar Plot





TEST NUMBER: P685251

CATALOG NUMBER: LX6C80D010 EX6809035 6LRMDLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94			
2	109	104	100	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	87	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78			
5	95	87	81	77	93	86	81	77	84	80	76	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	74	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	566698
5°	567784
10°	541100
15°	465922
20°	383826
25°	299787
30°	216508
35°	110878
40°	54066
45°	22467
50°	4094
55°	2380
60°	1557
65°	1154
70°	850
75°	763
80°	568
85°	0



TEST NUMBER: P685251

CATALOG NUMBER: LX6C80D010 EX6809035 6LRMDLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	967.1	14.0
10°-20°	2275.4	32.9
20°-30°	2253.6	32.6
30°-40°	1142.4	16.5
40°-50°	246.1	3.6
50°-60°	23.5	0.3
60°-70°	9.0	0.1
70°-80°	3.3	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5496.0	79.4
0°-40°	6638.4	95.9
0°-60°	6908.0	99.8
0°-90°	6921.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6921.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10337	
5°	10318	967
15°	8210	2275
25°	4956	2254
35°	1657	1142
45°	290	246
55°	25	23
65°	9	9
75°	4	3
85°	0	1
90°	0	



TEST NUMBER: P685251

CATALOG NUMBER: LX6C80D010 EX6809035 6LRMDLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10337.4
2.5°	10349.8
5°	10317.8
7.5°	10156.0
10°	9720.5
12.5°	9020.1
15°	8209.5
17.5°	7379.3
20°	6579.3
22.5°	5779.3
25°	4956.2
27.5°	4117.2
30°	3420.3
32.5°	2634.6
35°	1656.8
37.5°	1114.6
40°	755.5
42.5°	488.9
45°	289.8
47.5°	129.8
50°	48.0
52.5°	32.0
55°	24.9
57.5°	17.8
60°	14.2
62.5°	10.7
65°	8.9
67.5°	7.1
70°	5.3
72.5°	3.6
75°	3.6
77.5°	1.8
80°	1.8
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)