

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685263

Luminaire Tested: **LX6C90D010 EX6909027 6LBNLI**

Issue Date: 2/14/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P685263  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C90D010 EX6909027 6LBNLI  
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7408.0 lumens  
Efficiency: N/A  
Efficacy: 76.3 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 97.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685263

CATALOG NUMBER: LX6C90D010 EX6909027 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685263

CATALOG NUMBER: LX6C90D010 EX6909027 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85																			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80																			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76																			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72																			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62																			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	924613
5°	864669
10°	705203
15°	518936
20°	357684
25°	265546
30°	199461
35°	124383
40°	60377
45°	20715
50°	2721
55°	2055
60°	1173
65°	1388
70°	1715
75°	0
80°	0
85°	0



TEST NUMBER: P685263

CATALOG NUMBER: LX6C90D010 EX6909027 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1402.3	18.9
10°-20°	2517.0	34.0
20°-30°	2035.1	27.5
30°-40°	1172.3	15.8
40°-50°	247.8	3.3
50°-60°	21.4	0.3
60°-70°	10.6	0.1
70°-80°	1.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5954.4	80.4
0°-40°	7126.7	96.2
0°-60°	7396.0	99.8
0°-90°	7408.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7408.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16866	
5°	15713	###
15°	9144	2517
25°	4390	2035
35°	1859	1172
45°	267	248
55°	22	21
65°	11	11
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685263

CATALOG NUMBER: LX6C90D010 EX6909027 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	16866.3
2.5°	16663.6
5°	15712.8
7.5°	14345.5
10°	12668.5
12.5°	10948.9
15°	9143.6
17.5°	7402.5
20°	6131.2
22.5°	5159.3
25°	4390.1
27.5°	3738.7
30°	3151.0
32.5°	2499.6
35°	1858.6
37.5°	1292.4
40°	843.7
42.5°	512.8
45°	267.2
47.5°	106.7
50°	31.9
52.5°	31.9
55°	21.5
57.5°	21.5
60°	10.7
62.5°	10.7
65°	10.7
67.5°	10.7
70°	10.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)