

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684685

Luminaire Tested: **LX6C90D010 EX6C909030 6LBMDH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684685  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C90D010 EX6C909030 6LBMDH  
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS  
AND 6LRMD45 TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7005.9 lumens  
Efficiency: N/A  
Efficacy: 72.2 lumens/watt  
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 97.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684685

CATALOG NUMBER: LX6C90D010 EX6C909030 6LBMDH

### Luminous Intensity Polar Plot





TEST NUMBER: P684685

CATALOG NUMBER: LX6C90D010 EX6C909030 6LBMDH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	504806
5°	489180
10°	450454
15°	404026
20°	359487
25°	298529
30°	213280
35°	137099
40°	83542
45°	46439
50°	20571
55°	11918
60°	7850
65°	5565
70°	3927
75°	3029
80°	1926
85°	1258



TEST NUMBER: P684685

CATALOG NUMBER: LX6C90D010 EX6C909030 6LBMDH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	822.8	11.7
10°-20°	1991.7	28.4
20°-30°	2214.9	31.6
30°-40°	1312.4	18.7
40°-50°	480.8	6.9
50°-60°	120.8	1.7
60°-70°	44.1	0.6
70°-80°	15.3	0.2
80°-90°	3.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5029.5	71.8
0°-40°	6341.9	90.5
0°-60°	6943.5	99.1
0°-90°	7005.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7005.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	9208	
5°	8889	823
15°	7119	1992
25°	4935	2215
35°	2049	1312
45°	599	481
55°	125	121
65°	43	44
75°	14	15
85°	2	3
90°	0	



TEST NUMBER: P684685

CATALOG NUMBER: LX6C90D010 EX6C909030 6LBMDH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	9208.4
2.5°	9126.6
5°	8889.4
7.5°	8529.6
10°	8092.1
12.5°	7609.6
15°	7118.9
17.5°	6642.5
20°	6162.1
22.5°	5603.9
25°	4935.4
27.5°	4166.7
30°	3369.3
32.5°	2655.8
35°	2048.6
37.5°	1555.9
40°	1167.4
42.5°	850.5
45°	599.0
47.5°	380.3
50°	241.2
52.5°	169.7
55°	124.7
57.5°	94.0
60°	71.6
62.5°	55.2
65°	42.9
67.5°	32.7
70°	24.5
72.5°	18.4
75°	14.3
77.5°	10.2
80°	6.1
82.5°	4.1
85°	2.0
87.5°	2.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)