

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685278

Luminaire Tested: **LX6C90D010 EX6909040 6LBNLI**

Issue Date: 2/14/2022



**Test Information**

Test Method: LM-79-08  
Report Number: P685278  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/14/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C90D010 EX6909040 6LBNLI  
Description: 6 INCH 9000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS  
AND 6LBN TRIM WITH LI FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 7820.9 lumens  
Efficiency: N/A  
Efficacy: 80.5 lumens/watt  
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 97.1  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P685278

CATALOG NUMBER: LX6C90D010 EX6909040 6LBNLI

### Luminous Intensity Polar Plot





TEST NUMBER: P685278

CATALOG NUMBER: LX6C90D010 EX6909040 6LBNLI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95		
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89		
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85		
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80		
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76		
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72		
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68		
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65		
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62		
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	976161
5°	912875
10°	744520
15°	547869
20°	377624
25°	280347
30°	210583
35°	131316
40°	63741
45°	21870
50°	2866
55°	2170
60°	1239
65°	1466
70°	1811
75°	0
80°	0
85°	0



TEST NUMBER: P685278

CATALOG NUMBER: LX6C90D010 EX6909040 6LBNLI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1480.5	18.9
10°-20°	2657.4	34.0
20°-30°	2148.5	27.5
30°-40°	1237.7	15.8
40°-50°	261.6	3.3
50°-60°	22.6	0.3
60°-70°	11.2	0.1
70°-80°	1.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6286.4	80.4
0°-40°	7524.1	96.2
0°-60°	7808.3	99.8
0°-90°	7820.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7820.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	17807	
5°	16589	###
15°	9653	2657
25°	4635	2149
35°	1962	1238
45°	282	262
55°	23	23
65°	11	11
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685278

CATALOG NUMBER: LX6C90D010 EX6909040 6LBNLI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	17806.6
2.5°	17592.6
5°	16588.8
7.5°	15145.3
10°	13374.8
12.5°	11559.3
15°	9653.4
17.5°	7815.2
20°	6473.0
22.5°	5446.9
25°	4634.8
27.5°	3947.1
30°	3326.7
32.5°	2639.0
35°	1962.2
37.5°	1364.5
40°	890.7
42.5°	541.4
45°	282.1
47.5°	112.7
50°	33.6
52.5°	33.6
55°	22.7
57.5°	22.7
60°	11.3
62.5°	11.3
65°	11.3
67.5°	11.3
70°	11.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)