

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685038

Luminaire Tested: **LX6C05D010 EX6059027 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685038
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C05D010 EX6059027 6LBNLI
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 511.0 lumens
Efficiency: N/A
Efficacy: 71.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685038

CATALOG NUMBER: LX6C05D010 EX6059027 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685038

CATALOG NUMBER: LX6C05D010 EX6059027 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95																																				
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89																																				
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85																																				
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80																																				
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76																																				
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72																																				
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68																																				
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																																				
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62																																				
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	63778
5°	59647
10°	48646
15°	35795
20°	24671
25°	18316
30°	13762
35°	8580
40°	4165
45°	1427
50°	188
55°	143
60°	77
65°	91
70°	112
75°	0
80°	0
85°	0



TEST NUMBER: P685038

CATALOG NUMBER: LX6C05D010 EX6059027 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.7	18.9
10°-20°	173.6	34.0
20°-30°	140.4	27.5
30°-40°	80.9	15.8
40°-50°	17.1	3.3
50°-60°	1.5	0.3
60°-70°	0.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	410.7	80.4
0°-40°	491.6	96.2
0°-60°	510.2	99.8
0°-90°	511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1163	
5°	1084	97
15°	631	174
25°	303	140
35°	128	81
45°	18	17
55°	2	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P685038

CATALOG NUMBER: LX6C05D010 EX6059027 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1163.4
2.5°	1149.4
5°	1083.9
7.5°	989.5
10°	873.9
12.5°	755.2
15°	630.7
17.5°	510.6
20°	422.9
22.5°	355.9
25°	302.8
27.5°	257.9
30°	217.4
32.5°	172.4
35°	128.2
37.5°	89.2
40°	58.2
42.5°	35.4
45°	18.4
47.5°	7.4
50°	2.2
52.5°	2.2
55°	1.5
57.5°	1.5
60°	0.7
62.5°	0.7
65°	0.7
67.5°	0.7
70°	0.7
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)