

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136120

Luminaire Tested: **LD6A10D010TE ERW6A10827 6LW1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136120
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23374)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A10D010TE ERW6A10827 6LW1H
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 2700K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1078.0 lumens
Efficiency: N/A
Efficacy: 77.0 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.09
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 14
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136120

CATALOG NUMBER: LD6A10D010TE ERW6A10827 6LW1H

Luminous Intensity Polar Plot





TEST NUMBER: P136120

CATALOG NUMBER: LD6A10D010TE ERW6A10827 6LW1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	49	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	48474
5°	48351
10°	47897
15°	47563
20°	46600
25°	44839
30°	41516
35°	35354
40°	27074
45°	19117
50°	12910
55°	8167
60°	4763
65°	2177
70°	1354
75°	882
80°	451
85°	0



TEST NUMBER: P136120

CATALOG NUMBER: LD6A10D010TE ERW6A10827 6LW1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.0	6.5
10°-20°	198.1	18.4
20°-30°	284.7	26.4
30°-40°	273.8	25.4
40°-50°	163.0	15.1
50°-60°	67.2	6.2
60°-70°	16.9	1.6
70°-80°	3.9	0.4
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	552.7	51.3
0°-40°	826.5	76.7
0°-60°	1056.7	98.0
0°-90°	1078.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1078.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	743	
5°	738	70
15°	704	198
25°	623	285
35°	444	274
45°	207	163
55°	72	67
65°	14	17
75°	4	4
85°	0	0
90°	0	



TEST NUMBER: P136120

CATALOG NUMBER: LD6A10D010TE ERW6A10827 6LW1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	743.0
2.5°	739.5
5°	738.3
7.5°	732.4
10°	723.0
12.5°	713.6
15°	704.2
17.5°	690.0
20°	671.2
22.5°	648.8
25°	622.9
27.5°	591.1
30°	551.1
32.5°	501.6
35°	443.9
37.5°	381.5
40°	317.9
42.5°	259.1
45°	207.2
47.5°	163.7
50°	127.2
52.5°	97.7
55°	71.8
57.5°	51.8
60°	36.5
62.5°	23.6
65°	14.1
67.5°	9.4
70°	7.1
72.5°	4.7
75°	3.5
77.5°	2.4
80°	1.2
82.5°	1.2
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)