

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P710918

Luminaire Tested: **LD6C05D010 EU6059040 6LBHYH**

Issue Date: 10/18/2023



Test Information

Test Method: LM-79-08
Report Number: P710918
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-7)
Test Lab: INNOVATION CENTER
Issue Date: 10/18/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD6C05D010 EU6059040 6LBHYH
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND 6LCHYP TRIM WITH MW FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 525.3 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.59
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P710918

CATALOG NUMBER: LD6C05D010 EU6059040 6LBHYH

Luminous Intensity Polar Plot





TEST NUMBER: P710918

CATALOG NUMBER: LD6C05D010 EU6059040 6LBHYH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	96
2	110	106	103	100	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	92
3	106	101	97	94	105	100	96	93	97	94	92	95	93	91	93	91	89	88	88	88	88
4	103	97	92	89	101	96	92	88	94	90	87	92	89	86	90	87	86	84	84	84	84
5	99	92	88	84	97	92	87	84	90	86	83	88	85	83	87	84	82	81	81	81	81
6	95	89	84	81	94	88	83	80	86	83	80	85	82	79	84	81	79	78	78	78	78
7	92	85	80	77	91	84	80	77	83	79	76	82	79	76	81	78	76	75	75	75	75
8	89	82	77	74	88	81	77	74	80	76	73	79	76	73	78	75	73	72	72	72	72
9	86	79	74	71	85	78	74	71	77	73	71	77	73	70	76	73	70	69	69	69	69
10	83	76	71	68	83	76	71	68	75	71	68	74	70	68	73	70	68	67	67	67	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75400
5°	73404
10°	63682
15°	49138
20°	34245
25°	18049
30°	5045
35°	2235
40°	1109
45°	581
50°	247
55°	38
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P710918

CATALOG NUMBER: LD6C05D010 EU6059040 6LBHYH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.0	23.0
10°-20°	236.7	45.1
20°-30°	136.8	26.0
30°-40°	24.0	4.6
40°-50°	6.1	1.2
50°-60°	0.7	0.1
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	494.6	94.1
0°-40°	518.5	98.7
0°-60°	525.3	100.0
0°-90°	525.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1375	
5°	1334	121
15°	866	237
25°	298	137
35°	33	24
45°	8	6
55°	0	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P710918

CATALOG NUMBER: LD6C05D010 EU6059040 6LBHYH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1375.4
2.5°	1373.1
5°	1333.9
7.5°	1252.0
10°	1144.0
12.5°	1017.8
15°	865.8
17.5°	709.4
20°	587.0
22.5°	440.8
25°	298.4
27.5°	170.7
30°	79.7
32.5°	54.3
35°	33.4
37.5°	22.4
40°	15.5
42.5°	10.7
45°	7.5
47.5°	4.8
50°	2.9
52.5°	1.3
55°	0.4
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)