

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563955

Luminaire Tested: **LX6C05D010 EX6C059030 6LBMDH**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P563955
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2105-247-21)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C05D010 EX6C059030 6LBMDH
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LRMD45 TRIM WITH H FINISH, DIM TO WARM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 491.3 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.8
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 7.2
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P563955

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBMDH

Luminous Intensity Polar Plot





TEST NUMBER: P563955

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBMDH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	80	86	82	79	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			
6	88	79	73	69	86	78	73	69	77	72	68	75	71	68	74	70	67	66			
7	84	74	68	64	82	74	68	64	72	67	64	71	67	63	70	66	63	62			
8	80	70	64	60	78	70	64	60	68	63	60	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	60	56	64	59	56	63	59	56	54			
10	72	63	57	53	71	62	57	53	62	56	53	61	56	53	60	56	53	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35397
5°	34300
10°	31590
15°	28332
20°	25208
25°	20941
30°	14958
35°	9610
40°	5861
45°	3256
50°	1441
55°	832
60°	548
65°	402
70°	272
75°	212
80°	126
85°	63



TEST NUMBER: P563955

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBMDH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.7	11.7
10°-20°	139.7	28.4
20°-30°	155.3	31.6
30°-40°	92.0	18.7
40°-50°	33.7	6.9
50°-60°	8.5	1.7
60°-70°	3.1	0.6
70°-80°	1.1	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	352.7	71.8
0°-40°	444.7	90.5
0°-60°	486.9	99.1
0°-90°	491.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	491.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	646	
5°	623	58
15°	499	140
25°	346	155
35°	144	92
45°	42	34
55°	9	8
65°	3	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P563955

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBMDH

CANDELA DISTRIBUTION (FULL):

0°	
0°	645.7
2.5°	640.0
5°	623.3
7.5°	598.1
10°	567.5
12.5°	533.6
15°	499.2
17.5°	465.8
20°	432.1
22.5°	392.9
25°	346.2
27.5°	292.2
30°	236.3
32.5°	186.2
35°	143.6
37.5°	109.1
40°	81.9
42.5°	59.6
45°	42.0
47.5°	26.7
50°	16.9
52.5°	11.9
55°	8.7
57.5°	6.6
60°	5.0
62.5°	3.9
65°	3.1
67.5°	2.3
70°	1.7
72.5°	1.3
75°	1.0
77.5°	0.7
80°	0.4
82.5°	0.3
85°	0.1
87.5°	0.1
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)