

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P563959

Luminaire Tested: **LX6C05D010 EX6C059030 6LBWH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P563959  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C05D010 EX6C059030 6LBWH  
Description: 6 INCH 500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND 6LBW TRIM WITH H FINISH, DIM TO WARM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 601.1 lumens  
Efficiency: N/A  
Efficacy: 83.5 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 7.2  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P563959

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P563959

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20327
5°	20317
10°	20162
15°	20028
20°	19724
25°	19271
30°	18142
35°	16416
40°	13711
45°	10505
50°	7445
55°	4693
60°	2642
65°	1712
70°	1122
75°	826
80°	474
85°	503



TEST NUMBER: P563959

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	35.0	5.8
10°-20°	99.4	16.5
20°-30°	145.7	24.2
30°-40°	151.6	25.2
40°-50°	104.9	17.5
50°-60°	45.7	7.6
60°-70°	14.0	2.3
70°-80°	4.2	0.7
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.1	46.6
0°-40°	431.7	71.8
0°-60°	582.3	96.9
0°-90°	601.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	371	
5°	369	35
15°	353	99
25°	319	146
35°	245	152
45°	136	105
55°	49	46
65°	13	14
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P563959

CATALOG NUMBER: LX6C05D010 EX6C059030 6LBWH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	370.8
2.5°	371.6
5°	369.2
7.5°	366.1
10°	362.2
12.5°	358.4
15°	352.9
17.5°	345.8
20°	338.1
22.5°	329.5
25°	318.6
27.5°	304.5
30°	286.6
32.5°	267.9
35°	245.3
37.5°	220.4
40°	191.6
42.5°	162.9
45°	135.5
47.5°	109.9
50°	87.3
52.5°	66.2
55°	49.1
57.5°	35.1
60°	24.1
62.5°	17.9
65°	13.2
67.5°	10.2
70°	7.0
72.5°	5.5
75°	3.9
77.5°	2.3
80°	1.5
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)