

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685067

Luminaire Tested: **LX6C50D010 EX6509030 6LBMLI**

Issue Date: 2/15/2022

Test Information

Test Method: LM-79-08
Report Number: P685067
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C50D010 EX6509030 6LBMLI
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4826.0 lumens
Efficiency: N/A
Efficacy: 82.6 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685067
CATALOG NUMBER: LX6C50D010 EX6509030 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685067

CATALOG NUMBER: LX6C50D010 EX6509030 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	331086
5°	327938
10°	310749
15°	282130
20°	249303
25°	215535
30°	168482
35°	103323
40°	53035
45°	21072
50°	6840
55°	2361
60°	2017
65°	1608
70°	994
75°	1313
80°	0
85°	0



TEST NUMBER: P685067

CATALOG NUMBER: LX6C50D010 EX6509030 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	556.4	11.5
10°-20°	1385.2	28.7
20°-30°	1610.2	33.4
30°-40°	986.0	20.4
40°-50°	244.9	5.1
50°-60°	28.6	0.6
60°-70°	10.7	0.2
70°-80°	4.1	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3551.7	73.6
0°-40°	4537.8	94.0
0°-60°	4811.2	99.7
0°-90°	4826.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4826.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6040	
5°	5959	556
15°	4971	1385
25°	3563	1610
35°	1544	986
45°	272	245
55°	25	29
65°	12	11
75°	6	4
85°	0	0
90°	0	



TEST NUMBER: P685067

CATALOG NUMBER: LX6C50D010 EX6509030 6LBMLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6039.5
2.5°	6033.3
5°	5959.3
7.5°	5798.6
10°	5582.4
12.5°	5298.5
15°	4971.1
17.5°	4619.2
20°	4273.4
22.5°	3927.5
25°	3563.3
27.5°	3143.3
30°	2661.6
32.5°	2099.6
35°	1543.9
37.5°	1086.8
40°	741.1
42.5°	463.1
45°	271.8
47.5°	154.4
50°	80.2
52.5°	37.1
55°	24.7
57.5°	18.4
60°	18.4
62.5°	12.4
65°	12.4
67.5°	6.2
70°	6.2
72.5°	6.2
75°	6.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)