

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136153

Luminaire Tested: **LD6A15D010TE ERW6A15830 6LW1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136153
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23374)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A15D010TE ERW6A15830 6LW1H
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1505.0 lumens
Efficiency: N/A
Efficacy: 66.6 lumens/watt
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.09
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136153

CATALOG NUMBER: LD6A15D010TE ERW6A15830 6LW1H

Luminous Intensity Polar Plot





TEST NUMBER: P136153

CATALOG NUMBER: LD6A15D010TE ERW6A15830 6LW1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	49	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	67674
5°	67507
10°	66870
15°	66401
20°	65061
25°	62598
30°	57962
35°	49363
40°	37805
45°	26692
50°	18016
55°	11408
60°	6655
65°	3041
70°	1888
75°	1235
80°	601
85°	0



TEST NUMBER: P136153

CATALOG NUMBER: LD6A15D010TE ERW6A15830 6LW1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.7	6.5
10°-20°	276.5	18.4
20°-30°	397.4	26.4
30°-40°	382.2	25.4
40°-50°	227.6	15.1
50°-60°	93.8	6.2
60°-70°	23.6	1.6
70°-80°	5.4	0.4
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	771.6	51.3
0°-40°	1153.9	76.7
0°-60°	1475.3	98.0
0°-90°	1505.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1505.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1037	
5°	1031	98
15°	983	277
25°	870	397
35°	620	382
45°	289	228
55°	100	94
65°	20	24
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P136153

CATALOG NUMBER: LD6A15D010TE ERW6A15830 6LW1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1037.3
2.5°	1032.4
5°	1030.8
7.5°	1022.5
10°	1009.4
12.5°	996.2
15°	983.1
17.5°	963.4
20°	937.1
22.5°	905.8
25°	869.6
27.5°	825.3
30°	769.4
32.5°	700.3
35°	619.8
37.5°	532.6
40°	443.9
42.5°	361.7
45°	289.3
47.5°	228.5
50°	177.5
52.5°	136.4
55°	100.3
57.5°	72.3
60°	51.0
62.5°	32.9
65°	19.7
67.5°	13.2
70°	9.9
72.5°	6.6
75°	4.9
77.5°	3.3
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)