

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685068

Luminaire Tested: **LX6C50D010 EX6509030 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685068
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C50D010 EX6509030 6LBNLI
Description: 6 INCH 5000 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4287.9 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 58.4
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685068

CATALOG NUMBER: LX6C50D010 EX6509030 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685068

CATALOG NUMBER: LX6C50D010 EX6509030 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	535198
5°	500499
10°	408198
15°	300376
20°	207037
25°	153704
30°	115454
35°	71996
40°	34951
45°	11986
50°	1569
55°	1185
60°	680
65°	804
70°	994
75°	0
80°	0
85°	0



TEST NUMBER: P685068

CATALOG NUMBER: LX6C50D010 EX6509030 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	811.7	18.9
10°-20°	1456.9	34.0
20°-30°	1178.0	27.5
30°-40°	678.6	15.8
40°-50°	143.4	3.3
50°-60°	12.3	0.3
60°-70°	6.2	0.1
70°-80°	0.8	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3446.6	80.4
0°-40°	4125.2	96.2
0°-60°	4281.0	99.8
0°-90°	4287.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4287.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9763	
5°	9095	812
15°	5293	1457
25°	2541	1178
35°	1076	679
45°	155	143
55°	12	12
65°	6	6
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685068

CATALOG NUMBER: LX6C50D010 EX6509030 6LBNLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	9762.8
2.5°	9645.4
5°	9095.1
7.5°	8303.7
10°	7333.0
12.5°	6337.6
15°	5292.6
17.5°	4284.8
20°	3548.9
22.5°	2986.4
25°	2541.1
27.5°	2164.1
30°	1823.9
32.5°	1446.9
35°	1075.8
37.5°	748.1
40°	488.4
42.5°	296.8
45°	154.6
47.5°	61.8
50°	18.4
52.5°	18.4
55°	12.4
57.5°	12.4
60°	6.2
62.5°	6.2
65°	6.2
67.5°	6.2
70°	6.2
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)