

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136157

Luminaire Tested: **LD6A15D010TE ERW6A15930 6LW1H**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P136157  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23374)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6A15D010TE ERW6A15930 6LW1H  
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT  
WIDE DISTRIBUTION WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: (1) HIGH LUMEN LED 3000K  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1386.1 lumens  
Efficiency: N/A  
Efficacy: 61.3 lumens/watt  
Spacing Criteria (0/90/45): 1.13 / 1.13 / 1.09  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct

Input Watts (W): 22.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P136157  
CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1H

### Luminous Intensity Polar Plot





TEST NUMBER: P136157

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	104	110	107	105	102	103	101	99	99	98	96	96	94	93	91			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	84	83			
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75			
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68			
5	87	77	70	65	85	76	70	65	74	69	64	72	68	64	71	67	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51			
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47			
9	68	57	50	45	67	56	50	45	55	49	45	54	49	45	53	49	45	43			
10	64	53	46	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	62331
5°	62176
10°	61590
15°	61153
20°	59923
25°	57653
30°	53381
35°	45461
40°	34816
45°	24579
50°	16595
55°	10510
60°	6133
65°	2794
70°	1736
75°	1134
80°	564
85°	0



TEST NUMBER: P136157

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	90.0	6.5
10°-20°	254.7	18.4
20°-30°	366.0	26.4
30°-40°	352.0	25.4
40°-50°	209.6	15.1
50°-60°	86.4	6.2
60°-70°	21.8	1.6
70°-80°	5.0	0.4
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	710.7	51.3
0°-40°	1062.7	76.7
0°-60°	1358.7	98.0
0°-90°	1386.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1386.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	955	
5°	949	90
15°	905	255
25°	801	366
35°	571	352
45°	266	210
55°	92	86
65°	18	22
75°	4	5
85°	0	1
90°	0	



TEST NUMBER: P136157

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	955.4
2.5°	950.8
5°	949.4
7.5°	941.7
10°	929.7
12.5°	917.5
15°	905.4
17.5°	887.3
20°	863.1
22.5°	834.2
25°	800.9
27.5°	760.1
30°	708.6
32.5°	645.0
35°	570.8
37.5°	490.5
40°	408.8
42.5°	333.1
45°	266.4
47.5°	210.4
50°	163.5
52.5°	125.6
55°	92.4
57.5°	66.6
60°	47.0
62.5°	30.3
65°	18.1
67.5°	12.2
70°	9.1
72.5°	6.1
75°	4.5
77.5°	3.0
80°	1.5
82.5°	1.5
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)