

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P136037

Luminaire Tested: **LD6A15D010TE ERW6A15930 6LW1LI**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P136037
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23358)
Test Lab: INNOVATION CENTER P2
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LD6A15D010TE ERW6A15930 6LW1LI
Description: PORTFOLIO 6 INCH 60 DEGREE CUTOFF RECESSED DOWNLIGHT
WIDE DISTRIBUTION WITH SPECULAR CLEAR TRIM
Light Source: (1) HIGH LUMEN LED 3000K
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1470.8 lumens
Efficiency: N/A
Efficacy: 65.1 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.22 / 1.12
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22.6
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P136037

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1LI

Luminous Intensity Polar Plot





TEST NUMBER: P136037

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92	92	92	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84	84	84	84
3	100	93	88	83	98	92	87	83	89	85	81	87	83	80	84	81	79	77	77	77	77
4	94	86	80	75	93	85	79	75	83	78	74	81	76	73	79	75	72	70	70	70	70
5	89	80	73	68	87	79	73	68	77	71	67	75	70	67	73	69	66	65	65	65	65
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	69	64	61	59	59	59	59
7	79	69	62	57	77	68	61	57	66	61	57	65	60	56	64	59	56	54	54	54	54
8	74	64	57	53	73	63	57	52	62	56	52	61	56	52	60	55	52	50	50	50	50
9	70	60	53	49	69	59	53	48	58	52	48	57	52	48	56	51	48	46	46	46	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	44	43	43	43	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61802
5°	63381
10°	67705
15°	73108
20°	74295
25°	69739
30°	61427
35°	50024
40°	36332
45°	23315
50°	12251
55°	4186
60°	1200
65°	309
70°	191
75°	252
80°	0
85°	0



TEST NUMBER: P136037

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.1	6.4
10°-20°	303.6	20.6
20°-30°	440.5	30.0
30°-40°	388.1	26.4
40°-50°	198.7	13.5
50°-60°	41.8	2.8
60°-70°	3.2	0.2
70°-80°	0.7	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	838.3	57.0
0°-40°	1226.4	83.4
0°-60°	1466.9	99.7
0°-90°	1470.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1470.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	947	
5°	968	94
15°	1082	304
25°	969	441
35°	628	388
45°	253	199
55°	37	42
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P136037

CATALOG NUMBER: LD6A15D010TE ERW6A15930 6LW1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	947.3
2.5°	949.4
5°	967.8
7.5°	993.4
10°	1022.0
12.5°	1054.7
15°	1082.4
17.5°	1089.5
20°	1070.1
22.5°	1027.2
25°	968.8
27.5°	898.3
30°	815.4
32.5°	724.4
35°	628.1
37.5°	527.9
40°	426.6
42.5°	335.5
45°	252.7
47.5°	181.1
50°	120.7
52.5°	70.5
55°	36.8
57.5°	18.4
60°	9.2
62.5°	4.1
65°	2.0
67.5°	2.0
70°	1.0
72.5°	1.0
75°	1.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







(END OF REPORT)