

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684409

Luminaire Tested: **LX6C55D010 EX6C559027 6LBWH**

Issue Date: 2/15/2022

**Test Information**

Test Method: LM-79-08  
Report Number: P684409  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/15/2022  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LX6C55D010 EX6C559027 6LBWH  
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 2700K, 90CRI LEDS  
AND 6LBW TRIM WITH H FINISH  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5131.0 lumens  
Efficiency: N/A  
Efficacy: 80.3 lumens/watt  
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 63.9  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P684409

CATALOG NUMBER: LX6C55D010 EX6C559027 6LBWH

### Luminous Intensity Polar Plot





TEST NUMBER: P684409

CATALOG NUMBER: LX6C55D010 EX6C559027 6LBWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91			91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81			81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73			73
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65			65
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59			59
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53			53
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49			49
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44			44
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41			41
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38			38

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	173484
5°	173426
10°	172091
15°	170937
20°	168335
25°	164489
30°	154878
35°	140164
40°	117041
45°	89684
50°	63512
55°	40046
60°	22586
65°	14658
70°	9585
75°	7032
80°	4230
85°	4214



TEST NUMBER: P684409

CATALOG NUMBER: LX6C55D010 EX6C559027 6LBWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	298.9	5.8
10°-20°	848.1	16.5
20°-30°	1243.6	24.2
30°-40°	1294.3	25.2
40°-50°	895.4	17.5
50°-60°	389.9	7.6
60°-70°	119.6	2.3
70°-80°	35.8	0.7
80°-90°	5.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2390.6	46.6
0°-40°	3684.9	71.8
0°-60°	4970.2	96.9
0°-90°	5131.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5131.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3165	
5°	3152	299
15°	3012	848
25°	2719	1244
35°	2094	1294
45°	1157	895
55°	419	390
65°	113	120
75°	33	36
85°	7	5
90°	0	



TEST NUMBER: P684409

CATALOG NUMBER: LX6C55D010 EX6C559027 6LBWH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3164.6
2.5°	3171.3
5°	3151.5
7.5°	3124.9
10°	3091.5
12.5°	3058.3
15°	3011.9
17.5°	2951.9
20°	2885.5
22.5°	2812.3
25°	2719.4
27.5°	2599.6
30°	2446.7
32.5°	2287.0
35°	2094.4
37.5°	1881.7
40°	1635.5
42.5°	1389.6
45°	1156.8
47.5°	937.4
50°	744.7
52.5°	565.2
55°	419.0
57.5°	299.2
60°	206.0
62.5°	153.0
65°	113.0
67.5°	86.5
70°	59.8
72.5°	46.6
75°	33.2
77.5°	19.8
80°	13.4
82.5°	6.7
85°	6.7
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG







— 0°-180°







(END OF REPORT)