

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685092

Luminaire Tested: **LX6C55D010 EX6559030 6LBMLI**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P685092
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C55D010 EX6559030 6LBMLI
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBM TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5394.1 lumens
Efficiency: N/A
Efficacy: 84.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685092
CATALOG NUMBER: LX6C55D010 EX6559030 6LBMLI

Luminous Intensity Polar Plot





TEST NUMBER: P685092

CATALOG NUMBER: LX6C55D010 EX6559030 6LBMLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	370053
5°	366535
10°	347327
15°	315337
20°	278648
25°	240897
30°	188307
35°	115482
40°	59275
45°	23545
50°	7650
55°	2638
60°	2259
65°	1803
70°	1122
75°	1483
80°	0
85°	0



TEST NUMBER: P685092

CATALOG NUMBER: LX6C55D010 EX6559030 6LBMLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	621.9	11.5
10°-20°	1548.2	28.7
20°-30°	1799.7	33.4
30°-40°	1102.1	20.4
40°-50°	273.7	5.1
50°-60°	32.0	0.6
60°-70°	12.0	0.2
70°-80°	4.6	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3969.8	73.6
0°-40°	5071.8	94.0
0°-60°	5377.5	99.7
0°-90°	5394.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5394.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6750	
5°	6661	622
15°	5556	1548
25°	3983	1800
35°	1726	1102
45°	304	274
55°	28	32
65°	14	12
75°	7	5
85°	0	0
90°	0	



TEST NUMBER: P685092

CATALOG NUMBER: LX6C55D010 EX6559030 6LBMLI

CANDELA DISTRIBUTION (FULL):

	0°
0°	6750.3
2.5°	6743.4
5°	6660.7
7.5°	6481.1
10°	6239.5
12.5°	5922.1
15°	5556.2
17.5°	5162.8
20°	4776.4
22.5°	4389.7
25°	3982.6
27.5°	3513.3
30°	2974.8
32.5°	2346.7
35°	1725.6
37.5°	1214.7
40°	828.3
42.5°	517.6
45°	303.7
47.5°	172.6
50°	89.7
52.5°	41.5
55°	27.6
57.5°	20.6
60°	20.6
62.5°	13.9
65°	13.9
67.5°	7.0
70°	7.0
72.5°	7.0
75°	7.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)