

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P685093

Luminaire Tested: **LX6C55D010 EX6559030 6LBNLI**

Issue Date: 2/14/2022



Test Information

Test Method: LM-79-08
Report Number: P685093
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER
Issue Date: 2/14/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C55D010 EX6559030 6LBNLI
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBN TRIM WITH LI FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4794.1 lumens
Efficiency: N/A
Efficacy: 75.0 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P685093

CATALOG NUMBER: LX6C55D010 EX6559030 6LBNLI

Luminous Intensity Polar Plot





TEST NUMBER: P685093

CATALOG NUMBER: LX6C55D010 EX6559030 6LBNLI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89			
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85			
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80			
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76			
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72			
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68			
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65			
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62			
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	598351
5°	559563
10°	456365
15°	335825
20°	231469
25°	171845
30°	129077
35°	80495
40°	39073
45°	13404
50°	1757
55°	1329
60°	767
65°	908
70°	1122
75°	0
80°	0
85°	0



TEST NUMBER: P685093

CATALOG NUMBER: LX6C55D010 EX6559030 6LBNLI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	907.5	18.9
10°-20°	1628.9	34.0
20°-30°	1317.0	27.5
30°-40°	758.7	15.8
40°-50°	160.4	3.3
50°-60°	13.8	0.3
60°-70°	6.9	0.1
70°-80°	0.9	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3853.3	80.4
0°-40°	4612.0	96.2
0°-60°	4786.2	99.8
0°-90°	4794.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4794.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10915	
5°	10168	907
15°	5917	1629
25°	2841	1317
35°	1203	759
45°	173	160
55°	14	14
65°	7	7
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P685093

CATALOG NUMBER: LX6C55D010 EX6559030 6LBNLI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10914.8
2.5°	10783.6
5°	10168.4
7.5°	9283.5
10°	8198.3
12.5°	7085.4
15°	5917.2
17.5°	4790.4
20°	3967.7
22.5°	3338.8
25°	2841.0
27.5°	2419.4
30°	2039.1
32.5°	1617.6
35°	1202.8
37.5°	836.4
40°	546.0
42.5°	331.9
45°	172.9
47.5°	69.1
50°	20.6
52.5°	20.6
55°	13.9
57.5°	13.9
60°	7.0
62.5°	7.0
65°	7.0
67.5°	7.0
70°	7.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)