

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P684415

Luminaire Tested: **LX6C55D010 EX6C559030 6LBSH**

Issue Date: 2/15/2022



Test Information

Test Method: LM-79-08
Report Number: P684415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P204188)
Test Lab: INNOVATION CENTER
Issue Date: 2/15/2022
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LX6C55D010 EX6C559030 6LBSH
Description: 6 INCH 5500 LUMEN PORTFOLIO LED DOWNLIGHT WITH, 3000K, 90CRI LEDS
AND 6LBS TRIM WITH H FINISH
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6279.9 lumens
Efficiency: N/A
Efficacy: 98.3 lumens/watt
Spacing Criteria (0/90/45): 1.06 / 1.06 / 1.17
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 63.9
Input Voltage (V):
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P684415

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

Luminous Intensity Polar Plot





TEST NUMBER: P684415

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|---|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | | | | | | | | | | | | | | | | | |
| 1 | 111 | 107 | 104 | 101 | 108 | 105 | 102 | 99 | 101 | 98 | 96 | 97 | 95 | 93 | 93 | 92 | 90 | 88 | | | | | | | | | | | | | | | | | | | |
| 2 | 102 | 96 | 90 | 85 | 100 | 94 | 88 | 84 | 90 | 86 | 82 | 87 | 83 | 80 | 84 | 81 | 79 | 77 | | | | | | | | | | | | | | | | | | | |
| 3 | 95 | 85 | 78 | 73 | 92 | 84 | 77 | 72 | 81 | 75 | 71 | 78 | 74 | 70 | 76 | 72 | 69 | 67 | | | | | | | | | | | | | | | | | | | |
| 4 | 87 | 77 | 69 | 63 | 85 | 75 | 68 | 63 | 73 | 67 | 62 | 71 | 65 | 61 | 69 | 64 | 60 | 58 | | | | | | | | | | | | | | | | | | | |
| 5 | 81 | 69 | 61 | 55 | 79 | 68 | 61 | 55 | 66 | 60 | 55 | 64 | 59 | 54 | 63 | 58 | 53 | 51 | | | | | | | | | | | | | | | | | | | |
| 6 | 75 | 63 | 55 | 49 | 73 | 62 | 54 | 49 | 60 | 54 | 49 | 59 | 53 | 48 | 57 | 52 | 48 | 46 | | | | | | | | | | | | | | | | | | | |
| 7 | 70 | 58 | 50 | 44 | 68 | 57 | 49 | 44 | 55 | 49 | 44 | 54 | 48 | 43 | 53 | 47 | 43 | 41 | | | | | | | | | | | | | | | | | | | |
| 8 | 65 | 53 | 45 | 40 | 64 | 52 | 45 | 40 | 51 | 44 | 39 | 50 | 44 | 39 | 49 | 43 | 39 | 37 | | | | | | | | | | | | | | | | | | | |
| 9 | 61 | 49 | 41 | 36 | 60 | 48 | 41 | 36 | 47 | 40 | 36 | 46 | 40 | 36 | 45 | 40 | 35 | 34 | | | | | | | | | | | | | | | | | | | |
| 10 | 58 | 45 | 38 | 33 | 56 | 45 | 38 | 33 | 44 | 37 | 33 | 43 | 37 | 33 | 42 | 37 | 33 | 31 | | | | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 180051 |
| 5° | 179215 |
| 10° | 175514 |
| 15° | 169133 |
| 20° | 161352 |
| 25° | 152658 |
| 30° | 143997 |
| 35° | 135586 |
| 40° | 127668 |
| 45° | 119005 |
| 50° | 108508 |
| 55° | 95834 |
| 60° | 81112 |
| 65° | 63690 |
| 70° | 45440 |
| 75° | 24888 |
| 80° | 4388 |
| 85° | 0 |



TEST NUMBER: P684415

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 307.6 | 4.9 |
| 10°-20° | 836.2 | 13.3 |
| 20°-30° | 1161.2 | 18.5 |
| 30°-40° | 1267.2 | 20.2 |
| 40°-50° | 1182.1 | 18.8 |
| 50°-60° | 897.2 | 14.3 |
| 60°-70° | 491.3 | 7.8 |
| 70°-80° | 135.2 | 2.2 |
| 80°-90° | 1.9 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 2305.0 | 36.7 |
| 0°-40° | 3572.2 | 56.9 |
| 0°-60° | 5651.6 | 90.0 |
| 0°-90° | 6279.9 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 6279.9 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 3284 | |
| 5° | 3257 | 308 |
| 15° | 2980 | 836 |
| 25° | 2524 | 1161 |
| 35° | 2026 | 1267 |
| 45° | 1535 | 1182 |
| 55° | 1003 | 897 |
| 65° | 491 | 491 |
| 75° | 118 | 135 |
| 85° | 0 | 2 |
| 90° | 0 | |



TEST NUMBER: P684415

CATALOG NUMBER: LX6C55D010 EX6C559030 6LBSH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|--------|
| 0° | 3284.4 |
| 2.5° | 3284.4 |
| 5° | 3256.7 |
| 7.5° | 3215.2 |
| 10° | 3153.0 |
| 12.5° | 3070.0 |
| 15° | 2980.1 |
| 17.5° | 2869.5 |
| 20° | 2765.8 |
| 22.5° | 2641.3 |
| 25° | 2523.8 |
| 27.5° | 2406.3 |
| 30° | 2274.8 |
| 32.5° | 2150.3 |
| 35° | 2026.0 |
| 37.5° | 1901.5 |
| 40° | 1784.0 |
| 42.5° | 1659.5 |
| 45° | 1535.0 |
| 47.5° | 1410.5 |
| 50° | 1272.3 |
| 52.5° | 1140.9 |
| 55° | 1002.7 |
| 57.5° | 871.2 |
| 60° | 739.8 |
| 62.5° | 608.5 |
| 65° | 491.0 |
| 67.5° | 380.2 |
| 70° | 283.5 |
| 72.5° | 193.6 |
| 75° | 117.5 |
| 77.5° | 55.4 |
| 80° | 13.9 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |



Report Generated By 670246072 / DESKTOP-50001EG





— 0°-180°







(END OF REPORT)