

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P133541

Luminaire Tested: **LD6A30D010TE ERN6A30930 6LN1LI**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P133541  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P23397)  
Test Lab: INNOVATION CENTER P2  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: io LED  
Catalog Number: LD6A30D010TE ERN6A30930 6LN1LI  
Description: PORTFOLIO 6 INCH 50 DEGREE CUTOFF RECESSED DOWNLIGHT  
NARROW DISTRIBUTION WITH SPECULAR CLEAR TRIM  
Light Source: (1) HIGH LUMEN LED 3000K  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2564.6 lumens  
Efficiency: N/A  
Efficacy: 56.5 lumens/watt  
Spacing Criteria (0/90/45): 0.41 / 0.41 / 0.49  
Luminous Opening: Circular (Dia: 0.46' x H: 0')  
CIE Type: Direct


Input Watts (W): 45.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P133541

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P133541

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	87	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	85	79	76	91	84	79	75	82	78	75	81	77	74	80	77	74	73	73	73	73
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	70	69	69	69	69
8	85	77	72	68	84	76	71	68	75	71	68	74	70	68	74	70	67	66	66	66	66
9	82	74	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63	63	63
10	79	70	65	62	78	70	65	62	69	65	62	69	65	62	68	64	62	60	60	60	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	487661
5°	423280
10°	296184
15°	201802
20°	142334
25°	104817
30°	80403
35°	52613
40°	22833
45°	7307
50°	2192
55°	614
60°	470
65°	278
70°	343
75°	0
80°	0
85°	0



TEST NUMBER: P133541

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	551.7	21.5
10°-20°	841.5	32.8
20°-30°	678.8	26.5
30°-40°	406.2	15.8
40°-50°	77.8	3.0
50°-60°	6.3	0.2
60°-70°	2.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2072.0	80.8
0°-40°	2478.2	96.6
0°-60°	2562.4	99.9
0°-90°	2564.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2564.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7475	
5°	6463	552
15°	2988	841
25°	1456	679
35°	661	406
45°	79	78
55°	5	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P133541

CATALOG NUMBER: LD6A30D010TE ERN6A30930 6LN1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7474.8
2.5°	7195.8
5°	6463.3
7.5°	5471.6
10°	4470.9
12.5°	3633.9
15°	2987.8
17.5°	2476.6
20°	2050.1
22.5°	1718.9
25°	1456.1
27.5°	1245.5
30°	1067.3
32.5°	878.3
35°	660.6
37.5°	444.5
40°	268.1
42.5°	149.4
45°	79.2
47.5°	41.4
50°	21.6
52.5°	7.2
55°	5.4
57.5°	3.6
60°	3.6
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By E9808895 / USPTCWHP6082093







— 0°-180°







(END OF REPORT)